



Filter fan, Extract: W: 92 mm, H: 92 mm, RAL 7032, IP54, Airflow: 25 m³/h, U_e AC: 230 V, with Connecting cable 0.5m

Model	
product brand name	SIVACON
product designation	filter fan
design of the product	With connecting cable 0.5 m
type of ventilation	ventilation
fan design withdrawable fan	No
design of the product EMC version	No
General technical data	
A-rated sound power level maximum	30 dB
consumed active power rated value	12 W
cutout width	92 mm
cutout height	92 mm
operating period	37 500 h
rotor speed at 50 Hz rated value	2 700 1/min
rotor speed at 60 Hz rated value	3 200 1/min
type of voltage of the operating voltage	AC
operating voltage	
• at AC at 50 Hz rated value maximum	230 V
• at AC at 60 Hz rated value maximum	230 V
Protection class	
protection class IP	IP54
Appearance	
color	pebble grey
Product details	
product component fan	No
Number	
number of ventilators	1
Mechanical Design	
height	105 mm
width	105 mm
depth	60 mm
installation location	Control cabinet side panels, door, vertical
fastening method	snap-on mounting
fastening method	
• 19-inch installation	No
• wall mounting	Yes
net weight	0.5 kg
material	plastic
ambient temperature during operation	
• minimum	-10 °C

• maximum

55 °C

Approvals Certificates

General Product Approval	other	Environment
	Confirmation	Environmental Confirmations
	Miscellaneous	

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6423-2LV10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6423-2LV10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6423-2LV10

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

