



Product number 1175670110
EAN 4007123691890

DESCRIPTION

- 6 super-bright SMD LEDs at the front with up to 3 hours of illumination when the battery is fully charged.
- Additional switching level for 1 SMD LED in the light head.
- Functions: Spot - 100 % - 50 %.
- Rubberised surface for optimum grip.
- Bendable holding foot up to 200° with integrated magnet.
- 2 magnets on the back and two 360° swivelling hooks for flexible use.
- Integrated Li-Ion battery 3.7 V/2.5 Ah with charge indicator.
- On/off push button.
- USB C charging interface including 60 cm USB A to USB C charging cable.

TECHNICAL DATA

Luminous flux	500 lm	Number of batteries	1
Total luminous flux secondary source	120 lm	Battery type	Built-in battery pack
Colour temperature	6500 K	Battery technology	Lithium-ion
Colour rendering index	80-89 (class 1B)	Impact strength	IK07
Battery capacity	2.5 Ah	Protection class	III
Battery voltage	3.7 V	Degree of protection (IP)	IP20
Light duration max.	10 h	Colour	black/grey
Battery charging time approx.	4 h		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.46 kg
Weight of product (without packaging)	0.28 kg	Dimension LxWxH (incl. packing)	5 cm x 12.5 cm x 34 cm
Dimension LxWxH (without packing)	4.2 cm x 6.2 cm x 27.3 cm		

SCOPE OF DELIVERY

LED rechargeable hand lamp HL 501 A, 60cm USB A to USB C charging cable