



Part Number : [1200868373](#)
Product Description : Nano-Change (M8)
Single-Ended Cordset, 4 Poles, A-Coded, Male
(Straight) to Pigtail, 0.25mm² PUR/PVC Cable
2.0m (6.56') Length, PUR Cable Preferred
Version in Europe
Series Number : 120086
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 404006P02M020



Documents & Resources

Drawings
[1200868373_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Pigtail, 0.25mm ² PUR/PVC Cable 2.0m (6.56') Length, PUR Cable Preferred Version in Europe
IP Rating	IP67
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Single Ended
UPC	78172532222

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V

Physical

Cable Diameter	5.00mm (.197")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer

Material - Plating Mating	Gold
Net Weight	75.000/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	N/A