


Datasheet

Pressmaster original line crimp tool

RS Stock 447-459



Dimensions: (mm)





Features

- Small handle spread
- High strength, through-hardened alloy steel construction
- Interchangeable dies
- Ratchet with safety release
- Precise eccentric adjustment
- Laser marking available

Benefits

- Very comfortable and easy to use
- 50,000 cycle life span
- Versatile and easy to customize
- Ensures consistent performance

D Frame TECHNICAL SPECIFICATIONS		
Maximum Crimp Force:	1600 lbs.	7,000 N.
Maximum Handle Force:	90 lbs.	400 N.
Lifespan:	50,000 cycles	
Weight:	.75 lb.	340 g.
Length:	7.68"	195 mm
Open Handle Spread:	5.11"	130 mm
Closed Handle Spread:	2.55"	65 mm
Standard Die Width:	.394"	10 mm
Standard Die Height:	.394"	10 mm
Standard Die Length:	.945"	24 mm
Options:	Custom die sets, locators, packaging, instruction sheets, range of standard die sets available.	