

## EOS NOCUT WINTER VV913



HIGH PERFORMANCE POLYETHYLENE KNITTED GLOVE - DOUBLE NITRILE-COATING PALM

Ref. VV913



### Product specifications

High performance polyethylene support. TPR reinforcement on back and fingertips. Double smooth nitrile coating/foam nitrile on palm and fingertips. Embossed inside reinforcement on palm. Inside acrylic lining. Kevlar® thread on all the seams.

Support: High performance Polyethylene fibres.

Coating: nitrile.

Back reinforcement: TPR.

Reinforcement on thumb/forefinger: TPR.

Lining: Acrylic.

#### COLOUR

Yellow-Grey-Black

#### SIZE

08, 09, 10, 11

## Product Use - Risks



Cutting / Perforation



Cold / Weather



Wearing



Shock



Heavy industry



Construction / Civil engineering



Services / Logistics



Oil / Gas

## Product's highlights & user's benefits

0%  
SILICONE  
DWF



Double nitrile coating for oily work

1st smooth nitrile coating : impermeable to oils  
2nd nitrile foam coating : good adhesion



Flexible reinforcements

Increased protection from impacts and pinches



Reinforcement between the thumb and index finger and on the palm

Increased protection



Acrylic interior support

Excellent comfort all day long  
Maintains heat



Protection against impact in the metacarpal area. After an energy impact of 5J, the force transmitted to the back of the hand cannot exceed 4 kN.



Available only with header card

Very good resistance to abrasion and cutting

Increased lifespan

Kevlar® thread stitching

Increased lifespan

Washable

Increased lifespan

8 cm cuff with Velcro closure

Perfect adjustment  
Reduced discomfort at the wrist, during prolonged use

## Certifications and Standards



### REGULATION (EU) 2016/425

**EN420:2003+A1:2009 General requirements**  
5: Dexterity (from 1 to 5)

**EN388:2016 Protective gloves against mechanical Risks (Levels obtained on the palm)**

4: Resistance to abrasion (from 1 to 4)

X: Resistance to cutting (from 1 to 5)

4: Resistance to tear (from 1 to 4)

4: Resistance to puncture (1 to 4)

D: Resistance to cutting by sharp objects (TDM EN ISO 13997) (from A to F)

P: Protection against impact in metacarpal area (P) (EN13594:2002 6.8.2)



**EN511:2006 Protective gloves against cold (X = Unrealized test)**

1: Resistance to convective cold (from 1 to 4)

3: Resistance to contact cold (from 1 to 4)

X: Waterproof (0 or 1)





### USA STANDARDS



**ANSI-ISEA 105:2016 Hand protection**

A4: Resistance to cutting by sharp objects (from A1 to A9)

## References

References	Bar code	COLOUR	SIZE		
VV913JA08	3295249233051	Yellow-Grey-Black	08	60	6
VV913JA09	3295249233068	Yellow-Grey-Black	09	60	6
VV913JA10	3295249233075	Yellow-Grey-Black	10	60	6
VV913JA11	3295249233082	Yellow-Grey-Black	11	60	6