

Features

- A universal performer suitable for conveying many chemicals, solvents, fuels, oils, greases, compressed air and water.
- PVC Nitrile blend gives good abrasion and ageing resistance – superior to rubber.
- Clean, flexible and user-friendly.
- Reduced Plasticiser migration.
- High visibility triple stripe.
- Excellent resistance to UV / Ozone.
- Silicone and Cadmium free.
- Service Temperature - 15°C to + 60°C.

RS PRO Air Hoses

RS Stock No.: 0336847



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This is the cost-effective, high-performance TPE alternative to rubber hosing. While looking and feeling like rubber, it has many advantages including a longer lifespan. Manufactured from a hard wearing PVC Nitrile blend, this ergonomically-friendly super-flexible product is a real winner in many industrial environments.

Key Features:

- A universal performer suitable for conveying many chemicals, solvents, fuels, oils, greases, compressed air and water.
- PVC Nitrile blend gives good abrasion and ageing resistance – superior to rubber.
- Clean, flexible and user-friendly.
- Reduced Plasticiser migration.
- High visibility triple stripe.
- Excellent resistance to UV / Ozone.
- Silicone and Cadmium free.
- Service Temperature – 15°C to + 60°C.
- 3:1 safety factor.
- RoHS 3 compliant.
- BS EN ISO 5774 (Plastic hoses. Textile-reinforcement types for compressed-air applications.)

Composition:

- DEHP free PVC
- Polyester fiber reinforcement
- DEHP free nitrile PVC blend

Application:

- Construction
- Workshop environments
- General industrial use
- Garage forecourt

General Specifications

Hose Pipe / Flexible Tube	Flexible Tube
Colour	Black / Yellow
Features	Reinforced
Series	RS PRO GPA
Inner Diameter	13mm
Outer Diameter	22mm
Material	TPE
Hose Pipe Action	Transfer
Maximum Working Pressure	20bar
Suitable Application	Air / Water
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Length	100m
Reinforced	Yes
Bend Radius	85mm
Standards Met	ISO 5774