

Fluid control valve(2/2way)

2SA Series (Internally piloted and normally closed)



Symbol




Product feature

1. Indirect acting (Internal pilot) and normally closed type 2/2 way fluid valve. It can change direction quickly and has large flow.
2. It is compact, small and light weight. Easy to install and dismantle;
3. The valve body is made of SUS304. The coil has a Heat resistance classification of Class F. The standard seal material is FPM-F. Please contact us if other seal material are required.
4. The protection class of the coil is IP65 and there is a choice for grommet or terminal electrical entry.

Inner structure

2SA150(Grommet)



No.	Item
1	Body
2	Filter
3	Piston
4	Wear ring
5	O-ring
6	Cover
7	Screw
8	Spring
9	Spring
10	Spacer
11	Spring
12	Screw
13	Steel bushing
14	O-ring
15	Airtight ring
16	Fixed plate
17	O-ring
18	Movable core
19	Coil assembly
20	Coil nut

Specification

Model\Item	Port size [Note1]	Orifice size (Φmm)	Cv	Valid area or section (mm ²)	Weight [Note2](g)	Operating pressure differential		Proof pressure	
						MPa	psi	MPa	psi
2SA150-15	1/2"	15.0	5.50	100.0	575	Max:1.0 Min:0.05	Max:100 Min:10	1.5	220
2SA200-20	3/4"	20.0	9.50	170.0	735				
2SA250-25	1"	25.0	12.50	220.0	1035				
2SA320-32	1 1/4"	35.0	23.00	420.0	2288				
2SA400-40	1 1/2"	40.0	31.00	560.0	2678				
2SA500-50	2"	50.0	49.00	880.0	3558				

[Note1] PT thread, G thread and NPT thread are available.

[Note2] The weight in the table is the terminal valve's weight, Grommet valve's weight is 10g less than terminal's.

Specification of coil

Valve type	Coil type	Power type	Frequency (Hz)	Voltage range	Electrical entry	Power Consumption (VA/W)	Insulation	Temp. rise(°C)		
2SA150 2SA200 2SA250	CDA110 CLA110	AC	50	±15%	Terminal (CDA)	10.0VA	Class F	50		
			60			8.0VA		45		
		DC	-	±10%		6.5W		50		
2SA320 2SA400 2SA500	CDA160 CLA160	AC	50	±15%		Grommet (CLA)		25.0VA	Class F	65
			60					22.0VA		60
		DC	-	±10%				12.0W		50

Valve's specification

Acting	Internally piloted				
Initial state	Normally closed				
Adaptable fluid	Air, Water, Oil				
Viscosity limit	Under 20CST				
Ambient and fluid temperature (°C)		Water	Air	Oil	Ambient
	Max.	80	90	80	70
Min.	1	-20 [Note1]	-10 [Note2]	-20	

[Note1] Dew point: -20(°C) or less ;

[Note2] 50CST or less.

Ordering code

Ordering code of valves

2SA 150 15 A □ □

① ② ③ ④ ⑤ ⑥

① Model	② Orifice size	③ Port size	④ Voltage	⑤ Electrical entry	⑥ Thread type
2SA: 2/2 way internally piloted and normally closed	150: Φ15mm	15: 1/2"	A: AC220V B: DC24V C: AC110V E: AC24V F: DC12V	Blank: Terminal I: Grommet [Note]	Blank: PT G: G T: NPT
	200: Φ20mm	20: 3/4"			
	250: Φ25mm	25: 1"			
	320: Φ32mm	32: 1 1/4"			
	400: Φ40mm	40: 1 1/2"			
	500: Φ50mm	50: 2"			

[Note] The wire length is 0.5m.



Ordering code of accessories

Ordering code of accessories is the same as 2WA series valve's, Please refer to P171 for details of ordering code.

Fluid control valve(2/2way)


2SA Series (Internally piloted and normally closed)

Flow chart




Dimensions


2SA150~250 (Terminal)




2SA150~250(Grommet)



2SA320~500 (Terminal)



2SA320~500(Grommet)



Model\Item	A	AB	B	BA	C	D	E	EA	EB	EC	F	P
2SA150-15	73.5	67.5	44	27.5	112	77.5	6.5	8	65	35	29.5	1/2"
2SA200-20	75.5	79.5	51	33.5	119	87.5	6.5	8	75	38	33	3/4"
2SA250-25	77.5	90	57	40.5	126	93	6.5	8	80	42	35	1"
2SA320-32	120	-	76	52	156	-	-	-	-	-	-	1 1/4"
2SA400-40	126	-	86	58	166	-	-	-	-	-	-	1 1/2"
2SA500-50	144	-	96	70	177	-	-	-	-	-	-	2"

Model\Item	A	B	BA	C	D	E	EA	EB	EC	F	P
2SA150-15	67.5	44	27.5	102	77.5	6.5	8	65	35	29.5	1/2"
2SA200-20	79.5	51	33.5	109	87.5	6.5	8	75	38	33	3/4"
2SA250-25	90	57	40.5	116	93	6.5	8	80	42	35	1"
2SA320-32	120	76	52	147	-	-	-	-	-	-	1 1/4"
2SA400-40	126	86	58	155	-	-	-	-	-	-	1 1/2"
2SA500-50	144	96	70	170	-	-	-	-	-	-	2"

Fluid control valve(2/2 way)

2KSA Series (Internally piloted and normally opened)



Symbol



Product feature

1. Indirect acting (Internal pilot) and normally opened type 2/2 way fluid valve. It can change direction quickly and has large flow.
2. It is compact, small and light weight. Easy to install and dismantle;
3. The valve body is made of SUS304 . The coil has a Heat resistance classification of Class F. The standard seal material is FPM-F. Please contact us if other seal material are required.
4. The protection class of the coil is IP65 and there is a choice for grommet or terminal electrical entry .

Specification

Model\Item	Port size [Note1]	Orifice size (Φmm)	Cv	Valid area or section (mm ²)	Weight [Note2](g)	Operating pressure differentia		Proof pressure	
						MPa	psi	MPa	psi
2KSA150-15	1/2"	15.0	5.50	100.0	575	Max:0.7 Min:0.05	Max:100 Min:10	1.5	220
2KSA200-20	3/4"	20.0	9.50	170.0	735				
2KSA250-25	1"	25.0	12.50	220.0	1035				
2KSA320-32	1 1/4"	32.0	23.00	420.0	2287				
2KSA400-40	1 1/2"	40.0	31.00	560.0	2677				
2KSA500-50	2"	50.0	49.00	880.0	3557				

[Note1] PT thread, G thread and NPT thread are available.
 [Note2] The weight in the table is the terminal valve's weight.
 Grommet valve's weight is 10g less than terminal's.

Specification of coil


Valve type	Coil type	Power type	Frequency (Hz)	Voltage range	Electrical entry	Power Consumption (VA/W)	Insulation	Temp. rise(°C)	
2KSA150	CDA110	AC	50	±15%	Terminal (CDA)	15.0VA	Class F	50	
2KSA200			60			11.0VA		45	
2KSA250	DC	-	±10%	6.5W		50			
2KSA320				35.0VA		65			
2KSA400	CDA160	AC	50	±15%		Grommet (CLA)		30.0VA	60
2KSA500	60	30.0VA	60						
2KSA400	DC	-	±10%	12.0W	50				
2KSA500				12.0W	50				

Valve's specification

Acting	Internally piloted				
	Initial state	Normally opened			
Adaptable fluid	Air, Water, Oil				
Viscosity limit	Under 20CST				
Ambient and fluid temperature (°C)		Water	Air	Oil	Ambient
	Max.	80	90	80	70
	Min.	1	-20 [Note1]	-10 [Note2]	-20

[Note1] Dew point: -20(°C) or less ; [Note2] 50CST or less.

Inner structure



Ordering code

Ordering code of valves

① Model	② Orifice size	③ Port size	④ Voltage	⑤ Electrical entry	⑥ Thread type
2KSA: 2/2 way internally piloted and normally opened	150: Φ15mm	15: 1/2"	A: AC220V B: DC24V C: AC110V E: AC24V F: DC12V	Blank: Terminal I: Grommet [Note]	Blank: PT G: G T: NPT
	200: Φ20mm	20: 3/4"			
	250: Φ25mm	25: 1"			
	320: Φ32mm	32: 1 1/4"			
	400: Φ40mm	40: 1 1/2"			
	500: Φ50mm	50: 2"			

Ordering code of accessories



Ordering code of accessories is the same as 2WA series valve's. Please refer to P171 for details of ordering code.

[Note] The wire length is 0.5m.

Fluid control valve(2/2 way)


2KSA Series (Internally piloted and normally opened)

Flow chart




Dimensions


2KSA150~250 (Terminal)




2KSA150~250(Grommet)



2KSA320~500 (Terminal)



2KSA320~500(Grommet)



Model\Item	A	AB	B	BA	C	D	E	EA	EB	EC	F	P
2KSA150-15	73.5	67.5	44	27.5	112	77.5	6.5	8	65	35	29.5	1/2"
2KSA200-20	75.5	79.5	51	33.5	119	87.5	6.5	8	75	38	33	3/4"
2KSA250-25	77.5	90	57	40.5	126	93	6.5	8	80	42	35	1"
2KSA320-32	120	-	76	52	165.5	-	-	-	-	-	-	1 1/4"
2KSA400-40	126	-	86	58	175.5	-	-	-	-	-	-	1 1/2"
2KSA500-50	144	-	96	70	186.5	-	-	-	-	-	-	2"

Model\Item	A	B	BA	C	D	E	EA	EB	EC	F	P
2KSA150-15	67.5	44	27.5	109	77.5	6.5	8	65	35	29.5	1/2"
2KSA200-20	79.5	51	33.5	116	87.5	6.5	8	75	38	33	3/4"
2KSA250-25	90	57	40.5	123	93	6.5	8	80	42	35	1"
2KSA320-32	120	76	52	156.5	-	-	-	-	-	-	1 1/4"
2KSA400-40	126	86	58	164.5	-	-	-	-	-	-	1 1/2"
2KSA500-50	144	96	70	179.5	-	-	-	-	-	-	2"