



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Side Clip**

Primary Product Color: **Black**

Operating Temperature (Max): **125 °C [ 257 °F ]**

Operating Temperature Range: **-40 – 125 °C [ -40 – 257 °F ]**

Hardware Accessory Function: **Latching, Locking & Retention**

Features

Product Type Features

Connector Hardware Accessory Type	Side Clip
Hardware Accessory Function	Latching, Locking & Retention

Body Features

Primary Product Color	Black
-----------------------	-------

Dimensions

Product Length	36 mm
Product Height	34 mm

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2120339-1  
SIDE CLIP


Also in the Series | MotorMan




Circular Connector Contact Inserts(2)



Connector Caps & Covers(2)



Connector Hardware(4)




Connector Seals & Cavity Plugs(2)



[Connector Strain Relief\(2\)](#)



[Rectangular Connector Hoods & Bases \(4\)](#)



[Rectangular Contact Inserts\(5\)](#)

Customers Also Bought




TE Part #EL8206-000  
[HX-CT-50M-6.4-OUT-4](#)




TE Part #1-188685-2  
[STD TIMER PCB CONTACT](#)



TE Part #1103427-2  
[HC26.Bu.4.C.5,2](#)




TE Part #5433694001  
[CGPT-24/8-0-SP](#)



TE Part #1SNA233030R2600  
[RC610 1->100 HORIZONTAL](#)




TE Part #7-1452653-2  
[MCON 1.2 LL REC SRC AU](#)




TE Part #1SNA176665R0200  
[BJMI6-4](#)



TE Part #2120337-1  
[SINGLE WIRE SEAL](#)



TE Part #1SNA176664R0100  
[BJMI6-3](#)



TE Part #2-1768077-7  
[LBF-5107165400AB](#)

Documents

Product Drawings

[HG-Q-Buegel-100](#)

English

CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1245276-2\\_B.2d\\_dxf.zip](#)

English

[3D PDF](#)



3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1245276-2\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1245276-2\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[HG-Q8 - HOOD AND HOUSING](#)

English

[Product Specification](#)

English