



## SAFETY DATA SHEET

ELECTRACLEAN SPRAY

Page: 1

Revision date: 26/10/17

Revision No: 9

### Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

**Product name:** ELECTRACLEAN SPRAY

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Use of substance / mixture:** Cleaner for electronic items

#### 1.3. Details of the supplier of the safety data sheet

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

#### 1.4. Emergency telephone number

**Emergency tel:** +44 (0) 113 232 2600

### Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

**Classification under CLP:** Skin Irrit. 2: H315; Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Flam. Aerosol 1: H222; STOT SE 3: H336; -: EUH066; -: H229

**Most important adverse effects:** Repeated exposure may cause skin dryness or cracking. Extremely flammable aerosol. Pressurised container: May burst if heated. Causes skin irritation. Causes serious eye irritation. May cause drowsiness or dizziness. Toxic to aquatic life with long lasting effects.

#### 2.2. Label elements

**Label elements:**

**Hazard statements:** EUH066: Repeated exposure may cause skin dryness or cracking.

H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

[cont...]

# SAFETY DATA SHEET

## ELECTRACLEAN SPRAY

Page: 2

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark

GHS09: Environmental



**Signal words:** Danger

**Precautionary statements:** P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P251: Do not pierce or burn, even after use.

P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P285: In case of inadequate ventilation wear respiratory protection.

P302+352: IF ON SKIN: Wash with plenty of water/.

P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS - REACH registered number(s): 01-21194755-33-XXXX

EINECS	CAS	PBT / WEL	CLP Classification	Percent
927-510-4	64742-49-0	-	Flam. Liq. 2: H225; Aquatic Chronic 2: H411; Skin Irrit. 2: H315; STOT SE 3: H336; Asp. Tox. 1: H304; -: EUH066	>50%

#### PROPAN-2-OL

200-661-7	67-63-0	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	15-20%
-----------	---------	---	---	--------

#### CARBON DIOXIDE AEROSOL PROPELLANT

204-696-9	124-38-9	Substance with a Community workplace exposure limit.	Press. Gas: H280	1-10%
-----------	----------	--	------------------	-------

## Section 4: First aid measures

[cont...]

# SAFETY DATA SHEET

## ELECTRACLEAN SPRAY

Page: 3

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

[cont...]

# SAFETY DATA SHEET

ELECTRACLEAN SPRAY

Page: 4

## 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

## 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.  
Do not handle in a confined space. Avoid the formation or spread of mists in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

**Suitable packaging:** Must only be kept in original packaging.

### 7.3. Specific end use(s)

**Specific end use(s):** No data available.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	2,085mg/m <sup>3</sup>	-	-	-

**PROPAN-2-OL**

UK	400 ppm, 999 mg/m <sup>3</sup>	500 ppm, 1250 mg/m <sup>3</sup>	-	-
----	--------------------------------	---------------------------------	---	---

**CARBON DIOXIDE AEROSOL PROPELLANT**

UK	5000ppm 9150mg/m <sup>3</sup>	15000ppm 27400mg/m <sup>3</sup>	-	-
----	-------------------------------	---------------------------------	---	---

### DNEL/PNEC Values

**Hazardous ingredients:**

**HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS**

Type	Exposure	Value	Population	Effect
DNEL	Oral	149	Consumers	Local

[cont...]

# SAFETY DATA SHEET

## ELECTRACLEAN SPRAY

Page: 5

DNEL	Inhalation	447	Consumers	Local
DNEL	Inhalation	2085	Workers	Local
DNEL	Dermal	300	Workers	Local

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Protective gloves. Nitrile gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

**Environmental:** No data available

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Aerosol

**Colour:** Colourless

**Odour:** Characteristic odour

**Evaporation rate:** Fast

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Miscible

**Viscosity:** Non-viscous

**Boiling point/range°C:** >35

**Melting point/range°C:** < -60

**Flammability limits %: lower:** 1.1

**upper:** 13

**Flash point°C:** -5

**Autoflammability°C:** >200

**Relative density:** 0.74

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions. Decomposition may occur on exposure to conditions or materials listed below.

[cont...]

# SAFETY DATA SHEET

ELECTRACLEAN SPRAY

Page: 6

## 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

## 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

## 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Hazardous ingredients:**

#### HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS

DERMAL	RBT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>5000	mg/kg

#### PROPAN-2-OL

IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg
SCU	MUS	LDLO	6	gm/kg

**Relevant hazards for product:**

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

## Section 12: Ecological information

### 12.1. Toxicity

[cont...]

# SAFETY DATA SHEET

ELECTRACLEAN SPRAY

Page: 7

## Hazardous ingredients:

### HYDROCARBONS, C7, N-ALKANES, ISOALKANES, CYCLICS

Daphnia magna	96H LC50	>1 < 10	mg/l
FISH	96H LC50	>1 <10	mg/l

## 12.2. Persistence and degradability

**Persistence and degradability:** Not biodegradable.

## 12.3. Bioaccumulative potential

**Bioaccumulative potential:** Bioaccumulation potential.

## 12.4. Mobility in soil

**Mobility:** Readily absorbed into soil.

## 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

## 12.6. Other adverse effects

**Other adverse effects:** Toxic to aquatic organisms. Toxic to soil organisms.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Recovery operations:** No data available

**Waste code number:** 16 05 04

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

### 14.1. UN number

**UN number:** UN1950

### 14.2. UN proper shipping name

**Shipping name:** AEROSOLS, FLAMMABLE

### 14.3. Transport hazard class(es)

**Transport class:** 2.1

### 14.4. Packing group

**Packing group:** n/a

[cont...]

# SAFETY DATA SHEET

ELECTRACLEAN SPRAY

Page: 8

## 14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: Yes

## 14.6. Special precautions for user

Special precautions: No special precautions.

## 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Transport in bulk: No data available.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: No data available

### 15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** Contains only FDA listed ingredients. NSF K2 registered,  
This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.  
EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.  
Compiled in accordance with REACH.

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.  
H222: Extremely flammable aerosol.  
H225: Highly flammable liquid and vapour.  
H229: Pressurised container: May burst if heated  
H280: Contains gas under pressure; may explode if heated.  
H304: May be fatal if swallowed and enters airways.  
H315: Causes skin irritation.  
H319: Causes serious eye irritation.  
H336: May cause drowsiness or dizziness.  
H411: Toxic to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.