

Product information

34 52 130

Precision Electronics Gripping Pliers

DIN ISO 9655



- For very precise assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- With precision laser cut cross-shaping
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Half-round jaws
- With precision laser cut cross-shaping
- Ball bearing chrome steel, forged, multi stage oil-hardened




General

Article No.	34 52 130
EAN	4003773080312
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	61 g
Dimensions	130 x 51 x 20 mm
Standard	DIN ISO 9655
REACH compliant	no
RohS compliant	no

Technical details


Jaw length (B)	22.7 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	1.6 mm
Tips thickness (F)	1.6 mm
Head width (A)	11.2 mm



Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

technical change and errors excepted



Cross-shaping: precision laser cut for a secure grip in ultra fine mounting work

