

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LDC


ES

DIST


00

REVISIONS





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED FP00-0291-04	13DEC04	C.W	I.E



SECTION A-A



SECTION B-B



1	84696-1
FINISH	PART NO.

WIRE RANGE	INSULATION DIA
1.23/2.27mm ² AWG #16/#14	3/3.8mm ϕ

NOTES:

- 1 FINISH : 0.2 μ m MIN GOLD PLATING (CONTACT AREA) OVER Ni UNDER PLATING ALL OVER EXCEPT INSIDE OF CONTACT BOX
GOLD PLATING THK DID NOT CONTROL AT CONTACT TIP AREA


2. TOLERANCE UNLESS OTHERWISE SPECIFIED

- * ≤ 10 : ± 0.3
10 < * ≤ 30 : ± 0.35
30 < * ≤ 100 : ± 0.4
ANGLE: $\pm 3^\circ$

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED

0 PLC	± 0.30
1 PLC	± 0.35
2 PLC	± 0.40
3 PLC	± 0.40
4 PLC	± 0.40
ANGLES	$\pm 3^\circ$

MATERIAL

(COPPER ALLOY)

FINISH

SEE TABLE

DWN	3JAN'00
CHK	WY LEE
LTR	3JAN'00
APVD	LP TAN
PRODUCT SPEC	WL CHOO
APPLICATION SPEC	108-51030
VEIGHT	114-51009
CUSTOMER DRAWING	1.93g

AMPAMP MANUFACTURING
(SINGAPORE) PTE. LTD.

NAME			
TAB CONTACT "S" SIZE <DYNAMIC D-5000 SERIES>			
SIZE	CAGE CODE	DRAWING NO	
A3	00779	C=84696	
SCALE 4:1		SHEET 1 OF 1	REV B