



Part Number : [783532011](#)

Product Description : Impact 6 Pair, Right-Angle Power Header, Right Hold-Down, Module 1: Blade A1 & A2; B1 & B2 and C1 & C2 Length 6.90mm; Module 2: Blade A1 & A2; B1 & B2 and C1 & C2 Length 6.90mm; Press-Fit, LCP, Glass Filled UL94-V0, Black

Series Number : 78353

Status : Active

Product Category : Backplane Connectors



Documents & Resources

Drawings

[783532011_sd.pdf](#)

[PK-78353-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-78353-2011-001.zip](#)

Specifications

[AS-76060-9997-001.pdf](#)

[PS-78213-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	78353
Description	Impact 6 Pair, Right-Angle Power Header, Right Hold-Down, Module 1: Blade A1 & A2; B1 & B2 and C1 & C2 Length 6.90mm; Module 2: Blade A1 & A2; B1 & B2 and C1 & C2 Length 6.90mm; Press-Fit, LCP, Glass Filled UL94-V0, Black
Application	Conventional, Coplanar
Component Type	Power Header
Product Name	Impact
UPC	884982802575

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	20.0A
Data Rate	N/A

Shielded	No
Shield Type	N/A
Voltage - Maximum	250V

Physical

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	35.079/g
Number of Columns	N/A
Number of Pairs	6
Number of Rows	3
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.50mm
Pitch - Mating Interface	5.20mm
Pitch - Termination Interface	2.00mm, 3.20mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 6 Pair Vertical Power Receptacles	<u>78218</u>

Application Tooling