




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Backplate**

Primary Product Material: **Steel**

Operating Temperature (Max): **100 °C**

Operating Temperature Range: **-25 – 100 °C [-13 – 212 °F]**

Hardware Accessory Function: **Mounting**

Features

Product Type Features

Connector Hardware Accessory Type	Backplate
Hardware Accessory Function	Mounting

Body Features

Primary Product Plating Material	Nickel
Insulator Material	Polycarbonate Film Plus Acrylic Adhesive Layer
Primary Product Material	Steel

Usage Conditions

Operating Temperature (Max)	100 °C
Operating Temperature Range	-25 – 100 °C[-13 – 212 °F]

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC









Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2324271-1 RIGHT SEGMENT LGA4189-4 SOCKETP4 FOR ODM	 TE Part # 1-2324271-6 LEFT SEGMENT LGA4189-5 SOCKET-P5 FOR ODM	 TE Part # 1-2324271-8 LEFT SEGMENT LGA4189-5 SOCKET-P5 FOR ODM	 TE Part # 1-2324271-3 RIGHT SEGMENT LGA4189-4 SOCKETP4 FOR ODM
 TE Part # 1-2332283-2 LGA4189-4 SOCKET P4 KIT FOR ODM (15U AU)	 TE Part # 1-2332283-4 LGA4189-5 SOCKET P5 KIT FOR ODM (15U AU)	 TE Part # 1-2324271-5 RIGHT SEGMENT LGA4189-5 SOCKETP5 FOR ODM	 TE Part # 1-2324271-2 LEFT SEGMENT LGA4189-4 SOCKET-P4 FOR ODM



TE Part # 1-2332283-3
LGA4189-5 SOCKET P5 KIT FOR ODM (30U AU)

TE Part # 1-2332283-1
LGA4189-4 SOCKET P4 KIT FOR ODM (30U AU)

TE Part # 1-2324271-7
RIGHT SEGMENT LGA4189-5 SOCKETP5 FOR ODM

TE Part # 1-2324271-4
LEFT SEGMENT LGA4189-4 SOCKET-P4 FOR ODM

Customers Also Bought

TE Part #619400-1
1.0-2.3 Jack 2 posn Siemax, S

TE Part #1-2338987-1
QSFP28, 1X3, CAGE ASSY, SPRING, HS, LP

TE Part #4-1617753-9
FCA-325-BZ3

TE Part #ANT-916-CW-HWR-RPS
Antenna 1/2 Wave Whip Swivel 916MHz RPS

TE Part #1-2338987-2
QSFP28, 1X3, CAGE ASSY, SPRING, HS, LP

TE Part #1-1393230-1
RP3SL024

TE Part #1-2324271-3
RIGHT SEGMENT LGA4189-4 SOCKETP4 FOR ODM

TE Part #6766496-1
CONNECTOR, PIN, RIGHT ANGLE, SOLDER,FLAT

TE Part #CON SMA002-L
SMA Jack 50 Ohm PCB Through Hole

TE Part #2299804-1
NRW NON-FABRIC BOLSTER,P0,W/ COVER

Documents

Product Drawings

SOCKET P4/P5 BACKPLATE ASSY,STUD 7.12MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2330551-2_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-2330551-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2330551-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[LGA 4189 Socket and Hardware](#)

English

[1-1773982-5-lga_4189_flyer_cn](#)

English

Product Specifications

[Application Specification](#)

English