



APC Back-UPS Pro for Gaming, 2200VA/1320W, Tower, 230V, 4x Schuko and 2x IEC C13 outlets, RGB Lights, Pure Sine Wave, Midnight (Black)

BGM2200B-GR

#### **Overview**

Lead time	Usually in Stock	
Main		
Main Input Voltage	230 V AC 1 phase	
Other Input Voltage	230 V	
Main Output Voltage	230 V 1 phase	
Rated power in W	1320 W	
rated power in VA	2200 VA	
Product or component type	Uninterruptible power supply (UPS)	
Input Connection Type	Schuko	
output connection type	4 Schuko surge 2 IEC 60320 C13	
Cable length	1.5 m	
Number of cables	1	
Battery type	Lead-acid battery	
Range of product	Back-UPS Pro	

## **Batteries & Runtime**

Run Time	View Runtime Graph ☐	
Efficiency	View Efficiency Graph ☐	
Number of battery filled slots	1	
Number of battery free slots	0	
Battery recharge time	16 h	
Number of battery replacement quantity	1	
Battery voltage	24 V	
Overcurrent protection	15 A	
Battery charger power	12 W rated	
Battery life	35 year(s)	

## General

Rates duty January 2016

Provided equipment	safety guide USB cable power cable
product web sub-family	Gaming performance
Number preinstalled power module	0
Number of power module free slots	0
Redundant	No

# **Physical**

Colour	Black	
Height	292.1 mm	
Width	104.1 mm	
Depth	408.9 mm	
Net weight	12.34 kg	
Mounting support	Floor	
Mounting preference	No preference	
Mounting mode	Not rack-mountable	
Two post mountable	0	
USB compatible	Yes	
Mounting position	Vertical	

# Input

Network frequency	50/60 Hz +/- 3 Hz	
Plug standard	Schuko	
Input voltage limits	168302 V	
Maximum input current	12 A	
Switching current capacity	15 A	
Input harmonic distortion	Less than 3 % for full load	
Input protection type	Circuit breaker	

# Output

Maximum configurable power in W	1320 W	
Output frequency	50/60 Hz +/- 3 Hz sync to mains	
UPS type	Line interactive	
Wave type	Sine wave	
Full load runtime	00:00:30	
Half load runtime	00:04:19	
Maximum configurable power in VA	2200 VA	
Transfer time	8 ms typical : 10 ms maximum	

# Conformance

Product certifications	CE	
	СВ	

Equipment protection policy Lifetime : 50000 euros

## **Environmental**

Ambient air temperature for operation	040 °C	
Relative humidity	095 %	
Operating altitude	010000 ft	
Ambient air temperature for storage	-1540 °C	
Storage Relative Humidity	095 %	
Storage altitude	0.00000000003048.0000000000 m	
Acoustic level	45 dBA	
IP degree of protection	IP20	

# **Communications & Management**

Free slots	0	
control panel	Multifunction LCD status and control console	
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm	

# **Surge Protection and Filtering**

Surge energy rate	1080 J	
Noise suppression	Full time multi-pole noise filtering : 5% of IEEE surge let-through : zero clamping	

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	35.5 cm
Package 1 Length	48 cm
Package 1 Weight	14.52 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	30
Package 2 Height	90.6 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	450.50 kg
SCC14	20731304634762

# **Contractual warranty**

Warranty 2 years repair or replace, 3 years repair or replace for European Union countries



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

## 

Environmental Disclosure

Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	Ec96232c-7000-4722-846e-a372cdfca8dc
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No

# BGM2200B-GR

Image of product / Alternate images

**Alternative** 



