

Mod. 5215HL.B

5215HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE


Medium size watertight case, injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks.

Ideal container for mechanical equipment, optical equipment and electronic devices, valuables, outdoor equipment and more.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid



METRIC MM-KG-C°

**INTERNAL DIMENSIONS**

L LENGTH	520 mm
W WIDTH	285 mm
D DEPTH	150 mm
LID	55 mm
BASE	95 mm


EXTERNAL DIMENSIONS

L LENGTH	550 mm
W WIDTH	350 mm
D DEPTH	170 mm

OTHER DATA

WEIGHT EMPTY	2.55 Kg
WEIGHT WITH FOAM	3.05 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	22.2 lt
BUOYANCY	12.7 Kg/max
OPERATING TEMPERATURE	°C min -33 / max 90

IMPERIAL IN-LBS-F°



INTERNAL DIMENSIONS

L LENGTH	20 1/2 in
W WIDTH	11 1/4 in
D DEPTH	5 7/8 in
LID	2 3/16 in
BASE	3 3/4 in

EXTERNAL DIMENSIONS

L LENGTH	21 5/8 in
W WIDTH	13 3/4 in
D DEPTH	6 11/16 in

OTHER DATA

WEIGHT EMPTY	5.62 lbs
WEIGHT WITH FOAM	6.72 lbs
WEIGHT WITH CUSTOM	lbs
FOAM	
VOLUME	5.86 gal
BUOYANCY	27.99 lbs/max
OPERATING	°F min -27.4 / max
TEMPERATURE	194