

Rotary Hammers and Demolition Hammers

3

Rotary Hammers and Demolition Hammers






Immense power **for the toughest jobs.**

With the rotary hammers from 2–11 kg and the demolition hammers from 3–27 kg, Bosch offers everything that professionals need for extreme applications. The rotary hammers can be used for the hardest materials and offer immense power for fast work progress. What’s more, the Bosch Vibration Control reduces vibration and even makes long drilling and chiselling work more comfortable.

For example, the Demolition Hammer GSH 5-CE Professional: Unbeatably powerful with 40% less vibration



*in accordance with EPTA Standard 60745

Due to its Vibration Control the GSH 5 CE Professional has the lowest vibration level compared to other demolition hammers in this class, therefore enabling the longest operating time without interruption (187 mins).



Unbeatably powerful for the toughest jobs: the GSH 5 CE Professional masters any challenge, be it in plaster or concrete.

Rotary Hammer with SDS-plus

GBH 2-18 E Professional

The most compact and lightweight hammer in its class

- ▶ Extremely compact design and low weight of only 2 kg, ideal for working overhead
- ▶ High-torque motor and powerful hammer mechanism are optimised for fixing holes up to 10 mm
- ▶ Softgrip on main handle and gear housing


Other features

- ▶ Impact stop for drilling in wood and steel
- ▶ Softgrip on main handle and gear housing
- ▶ Overload clutch



Technical data	
Order number	0 611 258 ...
Impact energy	0 – 1.7 J
Impact rate at rated speed	0 – 3960 bpm
Rated speed	450 – 1550 rpm
Drilling dia. concrete, hammer drill bits	4 – 18 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 2K1
Auxiliary handle (2 602 025 102)	x
Carrying case	x
Depth stop 210 mm (2 603 001 019)	x

550 W 2.0 kg



Rotary Hammer with SDS-plus

GBH 2-18 RE Professional

The most compact and lightweight hammer in its class

- ▶ Extremely compact design and low weight of only 2 kg, ideal for working overhead
- ▶ High-torque motor and powerful hammer mechanism are optimised for fixing holes up to 10 mm
- ▶ Reverse operation for removing screws


Other features

- ▶ Softgrip on main handle and gear housing
- ▶ Impact stop for drilling in wood and steel
- ▶ Overload clutch



Technical data	
Order number	0 611 258 ...
Impact energy	0 – 1.7 J
Impact rate at rated speed	0 – 3960 bpm
Rated speed	450 – 1550 rpm
Drilling dia. concrete, hammer drill bits	4 – 18 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 3K1
Auxiliary handle (2 602 025 102)	x
Carrying case	x
Depth stop 210 mm (2 603 001 019)	x

550 W 2.0 kg



Rotary Hammer with SDS-plus**GBH 2-22 E Professional****The all-purpose workhorse that drills holes 30% faster**


- ▶ Revolutionary new impact mechanism ensures 30% faster drilling
- ▶ Control Electronic: accelerator function for sensitive drilling starts
- ▶ Overload clutch

Other features

- ▶ Impact stop for drilling in wood and steel
- ▶ Ergonomically designed softgrip handle with long trigger variable speed control
- ▶ Auxiliary handle with adjustable depth stop can be rotated 360°




Technical data	
Order number	0 611 250 ...
Impact energy	0 – 2.2 J
Impact rate at rated speed	0 – 4400 bpm
Rated speed	0 – 1000 rpm
Drilling dia. concrete, hammer drill bits	4 – 22 mm
Max. drilling dia. masonry, core cutters	68 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 604
Auxiliary handle (2 602 025 120)	x
Carrying case (2 605 438 524)	x
Depth stop 210 mm (1 613 001 010)	x

620 W 2.3 kg**Rotary Hammer with SDS-plus****GBH 2-22 RE Professional****The all-purpose workhorse that drills holes 30% faster**

- ▶ Revolutionary new impact mechanism ensures 30% faster drilling
- ▶ Control Electronic: accelerator function for sensitive pilot drilling
- ▶ Rotatable brush plate (equal power in forward and reverse direction)

Other features

- ▶ Reverse operation with extremely high torque for screwdriving operations
- ▶ Overload clutch
- ▶ Auxiliary handle with adjustable depth stop can be rotated 360°
- ▶ Ergonomically designed softgrip handle with long trigger variable speed control
- ▶ Softgrip for a secure hold

**620 W 2.3 kg**

Technical data	
Order number	0 611 250 ...
Impact energy	0 – 2.2 J
Impact rate at rated speed	0 – 4400 bpm
Rated speed	0 – 1000 rpm
Drilling dia. concrete, hammer drill bits	4 – 22 mm
Max. drilling dia. masonry, core cutters	68 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 704
Auxiliary handle	x
Carrying case (2 605 438 524)	x
Depth stop 210 mm (1 613 001 010)	x



Rotary Hammer with SDS-plus

GBH 2-26 E Professional

Faster than a speeding bullet – The sturdy tool for continuous use

- ▶ Superior drilling rate in the 2kg hammer class
- ▶ Easy-to-change toolholder
- ▶ 50 mm spindle collar diameter for more sturdiness


Other features

- ▶ Impact stop for drilling in wood and steel
- ▶ Ball grommet for preventing cable breaks
- ▶ Softgrip on main handle and auxiliary handle
- ▶ Overload clutch



Technical data	
Order number	0 611 251 ...
Impact energy	0 – 3 J
Impact rate at rated speed	0 – 4000 bpm
Rated speed	0 – 900 rpm
Drilling dia. concrete, hammer drill bits	4 – 26 mm
Max. drilling dia. masonry, core cutters	68 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 604
Auxiliary handle (2 602 025 141)	x
Carrying case (2 605 438 098)	x
Depth stop 210 mm (1 613 001 010)	x

800 W 2.7 kg



Rotary Hammer with SDS-plus

GBH 2-26 DFR Professional

Faster than a speeding bullet – The powerful all-rounder with quick-change chuck for daily use

- ▶ Superior drilling rate in the 2kg hammer class
- ▶ Exceptionally fast, tool-free changing between SDS-plus and quick-change chuck
- ▶ Rotation stop for chiselling


Other features

- ▶ Ball grommet for preventing cable breaks
- ▶ Softgrip on main handle and auxiliary handle for a secure hold



Technical data	
Order number	0 611 254 ...
Impact energy	0 – 3 J
Impact rate at rated speed	0 – 4000 bpm
Rated speed	0 – 900 rpm
Drilling dia. concrete, hammer drill bits	4 – 26 mm
Max. drilling dia. masonry, core cutters	68 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 76A
Auxiliary handle (2 602 025 141)	x
Carrying case (2 605 438 098)	x
Depth stop 210 mm (1 613 001 010)	x
Keyless chuck 13 mm (2 608 572 212)	x
Pointed chisel (SP no. 2 608 690 095)	x
SDS-plus quick-change chuck (2 608 572 213)	x
Set of concrete drill bits (6.5, 8, 10 mm)	x

800 W 2.9 kg



Rotary Hammer with SDS-plus**GBH 2-26 DRE Professional****Faster than a speeding bullet – The all-rounder for daily use**


- Superior drilling rate in the 2kg hammer class
- Rotation stop for chiselling
- Impact stop for drilling in wood and steel

Other features

- Easy-to-change toolholder
- Ball grommet for preventing cable breaks
- Softgrip on main handle and auxiliary handle for a secure hold
- Overload clutch
- Rotatable brush plate (for equal power in forward and reverse operation)
- 50 mm spindle collar diameter for more sturdiness




Technical data	
Order number	0 611 253 ...
Impact energy	0 – 3 J
Impact rate at rated speed	0 – 4000 bpm
Rated speed	0 – 900 rpm
Drilling dia. concrete, hammer drill bits	4 – 26 mm
Max. drilling dia. masonry, core cutters	68 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 704
Auxiliary handle (2 602 025 141)	x
Carrying case (2 605 438 098)	x
Depth stop 210 mm (1 613 001 010)	x

800 W 2.7 kg**Rotary Hammer with SDS-plus****GBH 4-32 DFR Professional****The fastest multi-hammer in the 4kg class**

- Wide range of applications in chiselling and drilling work and when working with a core cutter
- Drills up to 30% faster (25 mm diameter) than comparable competitor tools
- Low vibration values of only 8 m/s² for fatigue-free working due to Bosch Vibration Control



Technical data	
Order number	0 611 332 ...
Impact energy	0 – 5 J
Impact rate at rated speed	0 – 3600 bpm
Rated speed	0 – 760 rpm
Drilling dia. concrete, hammer drill bits	6 – 32 mm
Max. drilling dia. masonry, core cutters	90 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 100
Auxiliary handle (2 602 025 176)	x
Carrying case (2 605 438 651)	x
Depth stop 310 mm (1 613 001 003)	x
SDS-plus quick-change chuck (2 608 572 213)	x

New!**900 W 4.7 kg**

SP no. = Spare part number

Rotary Hammer with SDS-plus

GBH 4 DFE Professional

Perfect for all renovation work

- Components specially designed for heavy-duty use, for example hardened SDS drive jaws for long lifetime
- Exceptionally fast, tool-free changing between SDS-plus and quick-change chuck
- High single impact force ideal for chiselling and drilling


Other features

- Rotation stop for chiselling work
- Impact stop for drilling in wood and steel
- Accelerator electronics for precise pilot drilling with finely applied speed
- Overload clutch



Technical data	
Order number	0 611 236 ...
Impact energy	0 – 3.5 J
Impact rate at rated speed	0 – 3900 bpm
Rated speed	0 – 650 rpm
Drilling dia. concrete, hammer drill bits	4 – 30 mm
Max. drilling dia. masonry, core cutters	80 mm
Max. drilling dia. steel	13 mm
Scope of supply	... 704
Auxiliary handle (2 602 025 077)	x
Carrying case (2 605 438 389)	x
Depth stop 310 mm (1 613 001 003)	x
Grease tube (SP no. 1 615 430 005)	x
SDS-plus quick-change chuck (2 608 572 059)	x

750 W 3.9 kg



Dust Extraction Hammer with SDS-plus

GBH 2-23 REA Professional

The most compact solution for dust-free drilling

- Convenient working due to particularly compact design
- Integrated, removable dust extraction unit for clean, dust-free working
- Convenient working even overhead due to particularly compact design

Other features



- Core cutter adapter set for dust extraction when working with core cutters (up to 68 mm)
- Retaining valves prevent dust escaping
- Changeable micro-filter for cost-effective service
- Easy, tool-free removal of the dust extraction unit enables you to also work without dust extraction module
- Impact stop for drilling in wood and steel
- Transparent dust eye makes exact pilot drilling easier



Technical data	
Order number	0 611 250 ...
Impact energy	0 – 2.5 J
Impact rate at rated speed	0 – 4400 bpm
Rated speed	0 – 1000 rpm
Drilling dia. concrete, hammer drill bits	4 – 23 mm
Drilling dia. concrete, dust extraction unit	4 – 16 mm
Max. drilling dia. masonry, core cutters	68 mm
Drilling dia. concrete, dust extraction unit	4 – 16 mm
Scope of supply	... 500
Auxiliary handle (SP no. 1 619 P06 104)	x
Carrying case	x
Dust extraction unit	x
5 seal rings (SP no. 1 619 P06 107)	x







New!

710 W 2,9 / 3,6 kg





Range of applications for all SDS-plus hammers at a glance.

		Part number	Power input (watts)	Weight (kg)	Impact force (joules)	Drilling with/without impact, screwdriving	Chiselling
2-kilo Rotary Hammers							
GBH 2-18 RE Professional		0 611 258 ...	550	1.9	1.7		
GBH 2-22 RE Professional		0 611 250 ...	620	2.2	2.3		
GBH 2-23 REA Professional		0 611 250 ...	710	3.6	2.5		
GBH 2-26 DRE Professional		0 611 253 ...	800	2.7	3.0		
GBH 2-26 DFR Professional		0 611 254 ...	800	2.9	3.0		
GBH 2-26 DBR Professional		0 611 255 ...	900	2.9	3.0		
Cordless Rotary Hammers							
GBH 36 V-Li Compact Professional		0 611 903 ...	–	2.9	1.7		
GBH 36 V-Li Professional		0 611 900 ...	–	4.3	3.0		
GBH 36 VF-Li Professional		0 611 901 ...	–	4.5	3.0		
GBH 24 V/VF Professional		0 611 256 ...	–	3.8/3.9	1.3		
		0 611 262 ...					
4-kilo Rotary Hammers							
GBH 4-32 DFR Professional		0 611 332 ...	900	4.7	5.0		
GBH 4 DFE Professional		0 611 236 ...	750	3.9	3.5		

