

Product datasheet

Specifications



Rack PDU 2G, Metered-by-Outlet, ZeroU, 16A, 230V, (21) C13 & (3) C19

AP8459EU3

Overview

Presentation	APC Metered by Outlet Rack Power Distribution Units (PDUs) provide individual outlet power metering to enable energy optimization and circuit protection. Current metering provides real-time remote monitoring of connected loads. Metered by Outlet Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered by Outlet Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered by Outlet Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.
Lead time	Usually in Stock

Main

Colour	Black
Product or component type	PDU
PDU type	Metered outlet
Cord length	3.00 m
Provided equipment	CAN port terminator Installation guide Rack mounting brackets Safety guide Serial configuration cable

Complementary

Input Voltage	200 V 208 V 230 V
Height	182.9 cm
Width	5.6 cm
Output Voltage	230 V
Depth	5.1 cm
Net weight	6.76 kg
Mounting location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 16 A 2P + E
Mounting mode	Rack-mounted
Rack units	0U
Mounting position	Vertical

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Permissible voltage	100...240 V
Input current limits	16 A
Load capacity	3700 VA
Network frequency	50/60 Hz
Outlet type and quantity	21 IEC 60320 C13 3 IEC 60320 C19

Environment

Product certifications	UL listed VCCI class A VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC part 15 class A ICES-003
Ambient air temperature for operation	-5...60 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.0000000000...15240.0000000000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	203.7 cm
Package 1 Width	16.3 cm
Package 1 Length	11.7 cm
Package 1 Weight	9.03 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	4526
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACH Regulation	REACH Declaration

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	Yes
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins