

Termination board - IBS PCI SC/I-T - 2725260

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

PCI master controller board with electrical isolation



Product description

INTERBUS generation 4 controller board for PCs

With the IBS PCI SC/I-T standard controller, the high-level language programmable ISA bus platform is also extended towards PCI compatibility. The corresponding CMD INTERBUS configurator acts as the central interface to all other tools involved in an automation solution, such as EPLAN, visualization, and programming.

Interfaces that are consistent throughout the system, such as HLI and OPC, offer direct access to the INTERBUS fieldbus system as well as to the runtime system of the controller. Free drivers for Windows NT, XP, and Windows 7 round off the products.

The drivers are not supplied with the board. The necessary software is on the CD and in the user manual, or can be downloaded from this page.


The system packages offered include an inexpensive version consisting of the controller board, user manuals, all drivers (including HLI, but excluding OPC server), and CMD G4.

Why buy this product

- External 24 V DC power supply
- Direct integration into OPC-based visualization systems via OPC server
- Installation of several cards in a PC with monitoring of multiple INTERBUS lines
- Parameterization and diagnostics with Diag+
- Compatible driver
- Access to INTERBUS system data and controller data via visualization stations
- INTERBUS parameter channel (PCP) supported
- Access to high-level language applications via HFI



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 185121
Weight per Piece (excluding packing)	126.1 g
Custom tariff number	84733020
Country of origin	Germany

Termination board - IBS PCI SC/I-T - 2725260

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Height	107 mm
Depth	168 mm

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	0 °C ... 55 °C (acc. to EN 60204-1)
Ambient temperature (storage/transport)	-25 °C ... 75 °C (acc. to EN 60204-1)
Permissible humidity (operation)	75 % (on average, 85% infrequently, non-condensing)
Air pressure (operation)	860 hPa ... 1080 hPa (up to 2000 m above mean sea level)
Air pressure (storage/transport)	660 hPa ... 1080 hPa (up to 3000 m above sea level)

Control system

Control system	IBM-compatible PCs with PCI slot
Diagnostics tool	DIAG+ from version 1.0x
Configuration tool	CMD from version 4.5x

Software interfaces

Software driver	Windows NT
	Windows 2000
	Windows XP
	Windows 7
	Venturcom RTX 5.x
	Further types on request
Application interface	HFI
	OPC
	DDI

Software requirements

Configuration tool	CMD from version 4.5x
	Config+ from version 1.00 onwards
Diagnostics tool	DIAG+ from version 1.0x

Power supply

Power supply connection	Via PCI bus
Typical current consumption	0.7 A
Supply voltage	5 V DC
Supply voltage range	± 5 % (including ripple)

General

Weight	150 g
--------	-------

Termination board - IBS PCI SC/I-T - 2725260

Technical data

General

Format	Short plug-in card, 1-slot
--------	----------------------------

Data interfaces

Interface	INTERBUS remote bus
Connection method	9-pos. D-SUB female connector, with electrical isolation
Interface	Parameterization/operation/diagnostics
Connection method	RS-232-C, Mini-DIN female
Interface	Host system
Connection method	PCI bus, 32 bit, 33 MHz, 5 V
Interface	Direct I/Os
Connection method	14-pos. FLK pin strip
Interrupts	1 IRQ, PnP

Direct I/Os

Input name	Digital inputs
Number of inputs	6 (EN 61131-2 type 1)
Nominal input voltage U_{IN}	24 V DC
Output name	Digital outputs
Number of outputs	2
Connection method	FLK cable connector (14-pos.)
Maximum output current per channel	0.5 A

Fieldbus function

Amount of process data	max. 8192 Bit (INTERBUS-Master)
Number of supported devices	max. 512 (of which 254 are remote bus devices/bus segments)
Number of devices with parameter channel	max. 126
Module classification	INTERBUS master

Classifications

eCl@ss

eCl@ss 4.0	27240603
eCl@ss 4.1	27240603
eCl@ss 5.0	27242208
eCl@ss 5.1	27242208
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208
eCl@ss 8.0	27242208

ETIM

ETIM 2.0	EC001425
ETIM 3.0	EC001425

Termination board - IBS PCI SC/I-T - 2725260

Classifications

ETIM

ETIM 4.0	EC000236
ETIM 5.0	EC000236

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized

cUL Recognized

GOST

cULus Recognized

Termination board - IBS PCI SC/I-T - 2725260

Accessories

Accessories

Configuration and diagnostics

Software - IBS CMD SWT G4 E - 2721442



Network configuration software for INTERBUS Generation 4

Software - IBS CMD SWT G4 - 2721439



Network configuration software for INTERBUS Generation 4

Software - DIAG+ - 2730307



Diag+, diagnostics software, for INTERBUS networks, area of application: Startup, maintenance and, for example, for integration in control desk software, can be integrated in 32 bit applications (ActiveX-capable)

Software - CONFIG+ OEM - 2700779



Config+ project license, for configuration and diagnostics of an INTERBUS system. Please enter the project number in the configuration field or get in touch with your contact person in our sales organization.

Software - CONFIG+ DEMO - 2868046



Config+ demo version with restricted range of function (it is not possible to save projects)

Termination board - IBS PCI SC/I-T - 2725260

Accessories

Software - CONFIG+ - 2868059



Config+ full version for configuration and diagnostics of an INTERBUS system

Software - CONFIG+ CPY - 2868062



Config+ copy license makes it possible to install the Config+ software several times. A Config+ full version is necessary as well. When ordering, please state the number of licenses you need.

Drivers and interfaces

Software - IBS OPC SERVER - 2729127



INTERBUS OPC server, communication interface between distributed INTERBUS and Ethernet networks and visualizations.

Programming cable

Connecting cable - PRG CAB MINI DIN - 2730611



Connecting cable, for connecting the controller to a PC (RS-232) for PC Worx, 3 m in length

System cable

Cable - FLK 14/EZ-DR/ 50/KONFEK - 2288901



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 0.5 m

Termination board - IBS PCI SC/I-T - 2725260

Accessories

Interface module - UM 45-FLK14 - 2962557



VARIOFACE module, with screw connection and flat-ribbon cable connector, for assembly on NS 35/7.5, 14 positions

Driver software and documentation - CD PC DRIVER - 2985589



Driver software and documentation on CD-ROM (German and English)

Software - IBS PCI DDK - 2730271



Device driver development kit, for the development of device drivers for individual operating system (German, English)

Software drivers - CD IBS PCI SC RTX - 2737423



Driver and documentation CD incl. Driver as RTDLL, coupling driver for parallel Windows access and HLI interface as RTDLL, incl. online documentation (as development licence)
