



EN ISO 20344:2011



ENDURANCE
PORTORICO

81103-03L

S1P SRC

Size: 36-48
Weight: 650 gr.

Fit: 11

Working Environment:
Multipurpose, Logistics and Light Industry, Farming and Gardening, Wood-metal carpentry



FEATURES

UPPER

Grain leather Hydro 1,8-2,0 mm
3D Air circulation 320 gr.
nubuk-look leather 1,4-1,6 mm

LINING

3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Climaction-Fit 337

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Sandal

SOLE

PU DUAL-DENSITY SRC

Two-component PU sole with anti-wear scaff cap and high-comfort in-between insole. Outsole with self-cleaning tread pattern, with a formula designed to ensure greater grip. SRC Antislip standard.

TECHNOLOGIES

Removable Insole

337
climaction fit

Removable anatomic and ergonomic insole. Absorbent and transpiring open-cell foam support. Keeps feet fresh. Specifically-designed thermoforming for exceptional comfort.



Protection elements

KX RESISTANT TO 3.0 mm. NAILS **fibercap sxt**

Composite toe cap with fiberglass. Resistant to over 200J. Non metal perforation resistant insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

dynamic HC control
technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features

WED

Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other

DUALMICRO
DUALMICRO

Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.



SRC (SRA+SRB)



		SOLE B1 PU - PU
SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE °°) ≥0.28	0.52
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE °°) ≥0.13	0.23 0.18

EN ISO 20344:2011