

17" LED Monitor

Art. no. TVAC10011

Page 1 of 2



- Resolution: 1280 × 1024 pixels
- Fast response time (5 ms)
- LED background illumination: Superior colour display and contrast
- Graphical on-screen display (OSD)
- Connections: HDMI, VGA, 2 × BNC, cinch (audio), PC audio
- Integrated loudspeakers
- Low power consumption (LED technology)
- For wall and ceiling installation (with VESA mount)

The 17" LED monitor offers outstanding picture quality and fast reaction times for optimum picture fidelity. The integrated BNC connections and other interfaces equip the monitor with requirements for professional video surveillance. The signal is detected automatically, all settings can easily be made in the on-screen display in several languages. Thanks to energy-saving LED technology, the monitor has a low power consumption – and can be used efficiently for 24/7 operation.

Detailed surveillance pictures

With its high resolution, outstanding picture fidelity and fast reaction time, the monitor produces accurate surveillance pictures. The LED backlighting ensures optimum contrast and an extremely realistic color display.

Versatile connections

The video inputs as HDMI, VGA and BNC offer flexibility for connecting the monitor to a recorder, live-cameras or a computer. Integrated loudspeaker and audio inputs also allow soundtracks to be played. Therefore the monitor is a cost-effective component for versatile surveillance and IT systems.

Efficient uninterrupted 24/7 use

Thanks to high-quality industry components, the monitor is suitable for uninterrupted 24/7 use. The energy-efficient LED display ensures very low power consumption.

Easy installation

VESA standard mounts can be used to fix it to a wall or ceiling. This makes installation fast and easy.

17" LED Monitor

Art. no. TVAC10011

Page 2 of 2

Technical Data:

| | |
|-----------------------------------|--|
| Dimensions | 372 x 310 x 50 mm |
| Connections | 1 x HDMI, 1 x VGA, 2 x BNC, 1 x audio (3.5 mm jack), 2 x chinch audio, 1 x BNC-Out |
| Output | 1 x BNC |
| Horizontal/vertical viewing angle | 170° x 160° ° |
| Picture format | 4:3 |
| Screen diagonal | 17 " |
| Width | 372 mm |
| Gross weight | 4.6 kg |
| Display surface | matte |
| EAN | 4043158053531 |
| Input | 1 x HDMI, 1 x VGA, 2 x BNC, 1 x audio (3.5mm jack), 2 x chinch audio |
| Color levels | 16.7 MIO |
| Frequency range | 30 – 80KHz (H) / 50 – 75Hz (V) GHz |
| Housing material | Plastic |
| Brightness | 250 cd/m ² |
| Height | 310 mm |
| Comb filter | 3D |

| | |
|----------------------------|---------------------------------------|
| Contrast ratio | 1.000:1 |
| Loudspeaker | 2 x 2,5 W |
| Power consumption | max. 25 W W |
| Max. operating temperature | 40 °C |
| Max. humidity | max. 70 % |
| Min. operating temperature | 0 °C |
| Monitor type | LED |
| Net weight | 3.8 kg |
| Pixel pitch | 0.264 (H) x 0.264 (V) mm (H) x (V) mm |
| Reaction time | 5 ms |
| Signal detection | Automatic |
| DC voltage supply | 12 V |
| Power consumption | 3.000 mA |
| Video system | PAL / NTSC |