

FEATURES

- **2.5 m cable length:** Offers extended reach for versatile connections
- **IEC C13 to CEE 7 connectors:** Compatible with a wide range of devices and power sources
- **16 A current rating:** Supports high power devices safely
- **250 V voltage rating:** Suitable for standard electrical systems
- **Black PVC jacket:** Durable and resistant to wear, providing long-lasting protection
- **Right angle plug:** Saves space and allows for easy connections in tight spaces
- **Angled socket type:** Facilitates convenient cable management

RS PRO 2.5m Y Junction Power Cable, IEC C13 to CEE 7

RS Stock No: 558-960



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO Y Junction Power Cable is designed for efficient power distribution in various electrical setups. With a length of 2.5 metres, it provides flexibility and reach, making it ideal for connecting devices in both residential and commercial environments. The cable supports a current rating of 16 A and a voltage of 250 V, ensuring reliable performance for your power needs.

General Specifications

Connector Type A	IEC C13
Connector Type B	CEE 7
Jacket Colour	Black
Mains Socket Type	Angled
Product Type	Y Junction Power Cable

Mechanical Specifications

Cable Length	2.5 m
Jacket Material	Polyvinyl Chloride

Electrical Specifications

Current Rating	16 A
Mains Plug Type	Right Angle Plug
Voltage	250 V

Approvals

Standards/Approvals	CCCs, CEBEC, CSA, D, EAC, ENEC 11, FI, ICC, IMQ, JET, KEMA, KEUR, N, NF, OVE, PSE, RCM N10544, S, SII, UL, VDA
---------------------	--

