
3 Port Solenoid Valve Rubber Seal

Series SY100

Low power consumption: 0.5W (Standard, Without light)

(Current draw: 21mA at 24V DC)

*Large flow capacity style:0.75W (Current draw: 31mA at 24V DC)




Body width: 10mm

7.85 Ne/min (Standard style)
11.78 Ne/min (Large flow capacity style)

Exceedingly long life

100 million cycles (By SMC life test data)



Vacuum Applications Possible

Can be used up to -100kPa


Copper free

No copper used for sections in contact with fluids.

Bright colour tone and "state of the art" design

A bright grey concept has been adopted for this product to complement the surrounding operational environment.

SY100/ Application example (Pneumatic symbols shown are typical examples.)




Characteristics values indicated in this catalog are not guaranteed values but typical ones.




⚠ WarningOperation of Manual Override


Make sure that there is no danger, since manual override operation can make any connected equipment operate.


■Non-locking push style [Standard style] ■Locking slotted style [B] Press in the direction of the arrow. Turn in the direction of arrow.





■Push-locking slotted style [D] ■Push-locking lever style [E]





Pressing makes the valve operate. The valve can be locked in the manual override position by turning it to the direction that the arrow shows while keeping it pressed. If it is not turned, it can be used as a non-locking push style.

⚠ Caution


Gently operate locking manual override styles B, D using small screwdriver. [Torque: 0.1Nm or less]

∧ Caution

How to Use Plug Connector


①Connection/Disconnection of connector

- •Connection: Push the connector straight onto the pins of the solenoid, making sure the lip of the lever securely "locks" into the groove of the solenoid cover.
- Disconnecton: Press the lever against the connector housing and pull it outward from the solenoid.



2 Crimping connection of lead wire and socket

Strip 3.2 to 3.7mm of the lead wire ends, insert each stripped wire into a socket and crimp contact it using special crimping tool. Be careful that the outer insulation of the lead wires does not interfere with the socket contact part. Use exclusive crimping tool for crimping. (Contact SMC for special crimping tool.)




3Connection/Disconnection of socket with lead wire

Connection

Insert lead wire and crimped socket into square holes (indicated as A, B, COM) of connector. Press the socket in fully until the hook of the socket locks into the groove of the connector housing. Confirm the locked position by lightly pulling on the lead wire.

Disconnection


To remove the socket from the connector, pull out lead wire while depressing the hook of the socket with a fine screw driver (≅1mm). If the socket is to be re-used, reposition the hook again.



Plug Connector Lead Wire Length

Standard length is 300mm, but the following lengths are also available.

How to Order Connector Assembly



How to Order

To order a valve with lead wire length of other than 300mm, indicate part numbers of the valve without connector and the required connector ass'y separately. Example: 2000mm lead wire length

For DC SY114-5LO SY100-30-4A-20

Leau	wire length
_	300mm
6	600mm
10	1000mm
15	1500mm
20	2000mm
25	2500mm
30	3000mm
50	5000mm

I ead wire length


Surge Voltage Suppressor

<DC>

Grommet, L and M plug connector


■Standard style (With polarity) With surge voltage suppressor






Indicator light and surge voltage suppressor (□Z)






■Non-polar style



■Indicator light and surge voltage suppressor ("□U")



· Please connect correctly the lead wires to \bigoplus (positive) and \bigoplus (negative) indications on the connector.

For non-polar style, the lead wires can be connected to either one.

- · For DC voltages other than 12, 24V DC, incorrect wiring will cause damage to the surge voltage suppressor circuit. (Wrong polarity will cause trouble.)
- Solenoids, whose lead wires have been pre-wired: positive side red and negative side black.

⚠ Caution


Since there is some residual voltage according to the protection device and rated voltage in case of voltage surge suppressor by zener diode, pay attention to the surge protection on the controller side. (Diode residual voltage: $\cong 1V$)

Connector Assembly with Protective Cover


Connector assembly with protective cover enhances dust protection.

- •Effective in preventing possible short circuit problems due to contaminants in contact with connector section.
- Cover material is chloroprene rubber which has excellent weatherability and electric insulation properties. However, be careful not to allow contact with cutting oil.
- •Round cord provides neat appearance.

How to Order



Connector Assembly with Cover/Dimension



●How to Order

Indicate part number of connector assembly with cover in addition to the solenoid valve part number without connector of the plug connector.

<Example 1> Lead wire length: 2000mm

SY114-5LOZ-M3-Q SY100-68-A-20

<Example 2> Lead wire length: 300mm (Standard)

SY114-5LPZ-M3-Q

Symbol of connector assembly with cover

*No part numbers of connector assembly with cover are needed to be indicated in this case.

3 Port Direct Operated Rubber Seal

Series SY100

Model




Body ported



Base mounted

JIS Symbol





			Operating	Vacuum appl	ication (MPa)		Weight (g) (2)		
Actuation	Model	Model Style pressure range (MPa) P port R por			Effective area (mm²) (Nt/min)	Grommet style	L, M Plug connector		
N.C.	SY11 ³	Standard	0 to 0.7	-100kPa to 0.6	-100kPa to 0	0.14 (7.85)			
N.C.	SY11 ³ A	Large flow capacity	0 to 0.7	-100kPa to 0.6	-100kPa to 0	0.22 (11.78)	SY1□3 (A): 13 SY1□4 (A): 24		
N.O.	SY123 ⁽¹⁾	Standard	0 to 0.7	-100kPa to 0	-100kPa to 0.6	0.14 (7.85)	(Without sub-plate 12)	(Without sub-plate 14)	
N.O.	SY12 ₄ ³ A	Large flow capacity	0 to 0.7	-100kPa to 0	-100kPa to 0.6	0.22 (11.78)			

Note 1) SY123/SY124 and SY123/SY124 A: Supply pressure to 1(R) port and exhaust air from 3(P) port. Note 2) Value for DC.

Specifications

Fluid	Air					
Ambient and fluid temperature (°C)	Max. 50°C					
Response time (ms) (1)	10ms or less					
Max. operating frequency (Hz)	20					
Manual override	Non-locking push, Locking slotted, Push-locking slotted, Push-locking lever					
Lubrication	Not requited					
Mounting position	Free					
Impact/Vibration resistance (m/s2) (2)	150/30					
Enclosure	Dust-proof					

Note 1) According to dynamic performance test JIS B8374-1981 (Coil temperature 20°C, at rated voltage, without surge suppressor.)

Note 2) Impact resistance: No malfunction from tests using drop impact tester, to axis and right angle direction of main valve and armature, each one time when energized and de-energized. (Value in the inital stage)


Vibration resistance: No malfunction from tests with 8.3~2000Hz 1 sweep, to axis and right angle direction of main valve and armature, each one time when energized and de-enegized. (Value in the initial stage.)

Solenoid Specifications


Series		SY1 13 24	SY1 ¹³ A			
Electrical entry		Grommet (G), (H), L plug connector (L), M plug connector (M)				
Coil rated voltage (V)	DC	24, 12, 6, 5, 3				
Allowable voltage		-10 to +10%				
Power consumption (W)	(1) DC	0.5W (With light: 0.55W)	0.75W (With light: 0.8W)			
Surge voltage suppres	sor	Diode				
Indicator light		LED				

⁽¹⁾ At rated voltage

How to Order





How to Order



Construction

SY114, SY114A






Component Parts

No.	Description	Material	Notes		
1	Body	Resin	Gray		
2	Cover	Resin	Gray		
3	Push rod	Resin	_		
4	Armature ass'y	NBR/Stainless steel	_		
(5)	Core	Stainless steel	_		
6	Exhaust poppet	NBR	_		
7	Return spring	Stainless steel	_		
8	Poppet spring	Stainless steel	_		
9	Coil ass'y	_	_		

Replacement Parts


No.	Description	Part No.	Material			
10	Sub-plate	SY100-74-1-Q	Zinc die cast			
11)	Gasket	VJ100-6-1-Q	NBR			


How to Order Connector Assembly





Body Ported

Grommet (G), (H): $SY1_2^13$ (A)- $\Box_H^G\Box\Box$ -PM3 (-F) -Q












Base Mounted (With Sub-plate)

Grommet (G), (H): SY1 ¹₂4 (A)-□ ^G_H□□-M3-Q





Series **SY100 Manifold**



Specifications

Туре		30 ⁽⁴⁾	31	S41		
Manifold style		Sing	gle base style, B mou	ınt		
P (SUP)/R (EXH)	style	Comr	non SUP/Common E	XH		
Valve stations		2 to 10 stations	2 to 20	stations		
A porting	Location	Va	Base			
A porting	Direction	To	Тор			
D. d. i.e.	P, R port					
Port size	A port	М	3	M3 , M5		
	SY1□3	0.14 (_			
Valve effective	SY1□3A	0.21 (11.78)	_		
area	SY1□4	_	0.13 (6.87)			
mm² (Ne/min)(1)	SY1□4A	_	0.2 (10.8)			



Note 1) When mounted on manifold base

Note 1) When mounted on manifold base


Note 2) SY114 (A) and SY124 (A) can not be mounted on the same manifold.

Note 3) Supply to R port and exhaust from P port for SY124 (A).

Note 4) 30 Type is applicable only for SY113 and SY113A. Piping to exhaust port is not possible.

How to Order Manifold Base (Ordering Example)

Example



SS3Y1-S41-05-M5-Q·······1set (S41 type 5-station manifold part number)

SY100-77-1A-Q....1set (Blank plate assembly part number)

SY114-5GZ-Q....4set (Valve)


List part numbers of the installed valve and option in required station location separately under manifold part number.

Protective class class III (Mark:﴿)




Common SUP/Common EXH

30 Type




How to Order



Applicable solenoid valve (1) SY113-□□□-M3-Q


SY113A-UUUU-M3-Q Applicable blank plate assembly

SY100-77-1A-Q



31 Type R port P port

How to Order



Applicable solenoid valve (1)

SY113-□□□-M3-Q

SY113A-□□□□-M3-Q

SY123-□□□-M3-Q SY123A-□□□□-M3-Q


Applicable blank plate

assembly SY100-77-1A-Q




Note 1) SY113 (A) and SY123 (A) cannot be mounted on the same manifold.

S41 Type



How to Order



Applicable solenoid valve (1)


SY114-□□□□-Q

SY114A-□□□□-Q SY124-□□□□-Q

SY124A-□□□□-Q

Applicable blank plate assenbly

SY100-77-1A-Q







Protective class class III (Mark: ١٠)

Combination with Solenoid Valve and Gasket Manifold Base

Body ported




Base mounted



Blank Plate Assembly

Parts No.: SY100-77-1A-Q



Applicable base

Sub-plate (For body ported style) SS3Y1-30 type Manifold base SS3Y1-31 type

Applicable base

Sub-plate SS3Y1-S41 type manifold base

Applicable base

Sub-plate SS3Y1-30 type


SS3Y1- 31 type Manifold base


SS3Y1- S41 type



30 Type Manifold: Top Ported/SS3Y1-30-Station -F-Q

Grommet (G), (H)








No bracket is assembled prior to delivery.
 Mount one to the appropriate position.
 (Attach two brackets if more than five stations.)


L plug connector (L)



*Other dimensions are same as grommet style.

Station	2	3	4	5	6	7	8	9	10
	20.5	31	115	52	62.5	73	83.5	94	104.5

M plug connector (M)







* Other dimensions are same as grommet style.




31 Type Manifold: Top Ported/SS3Y1-31-Station-Q


Grommet (G), (H)








L plug connector (L)



* Other dimensions are same as grommet style.

M plug connector (M)



*Other dimensions are same as grommet style.


Station	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L ₁	33.5	44	54.5	65	75.5	86	96.5	107	117.5	128	138.5	149	159.5	170	180.5	191	201.5	212	222.5
L ₂	27.5	38	48.5	59	69.5	80	90.5	101	111.5	122	132.5	143	153.5	164	174.5	185	195.5	206	216.5




S41 Type Manifold: Side Ported/SS3Y1-S41-Station -M3/M5-Q


Grommet (G), (H)


In case of M5







In case of M3







L plug connector (L)





M plug connector (M)





Station	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L ₁	33.5	44	54.5	65	75.5	86	96.5	107	117.5	128	138.5	149	159.5	170	180.5	191	201.5	212	222.5
L2	27.5	38	48.5	59	69.5	80	90.5	101	111.5	122	132.5	143	153.5	164	174.5	185	195.5	206	216.5



Series SY Made to Order





Power Saver


Power consumption is decreased by 1/3 of standard product by reducing electrical power at holding. (This is effective when energizing time exceeds 62ms at rated voltage of 24V DC.)

Specifications

Series		SY1 ¹³ ₄ T	SY1 ¹³ AT			
Coil rated voltage	e (V)	24, 12V DC				
Power	Inrush	0.55	0.8			
consumption (W)	Holding	0.22	0.3			


Specifications except those mentioned above are same at standard.

How to Order




Operating principle

Power consumption at holding is decreased with the below indicated circuit, for energy savings. Refer to electrical power wave form shown below.



<Electrical wave form of power saving style, $SY1_{24}^{13}T>$



<Electrical wave from of power saving style, SY1¹³₂₄AT>

