




Connectors > Connector Accessories > Connector Caps & Covers > Bus Connector: Strain Relief, ATA



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Black**

Primary Product Material: **Thermoplastic**

[All Bus Connector: Strain Relief, ATA \(13\)](#)

Features

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Body Features

Primary Product Color	Black
Primary Product Material	Thermoplastic

Dimensions

Product Width	6.1 mm[.24 in]
Product Length	81.03 mm[3.19 in]
Product Height	14.76 mm[.581 in]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features

Packaging Method	Bag & Box
Packaging Quantity	500



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1-1761607-6
IDC LOW PRO HDR 60P RA LAT



TE Part # 1-1658621-1
60 NOVO MIL/CTR 15DP,LEAD FREE




TE Part # 1-5088450-1
PULL LOOP, CUT LENGTH 2.80 IN




TE Part # CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS




TE Part # 1-1658622-1
60 NOVO MIL/CTR 30DP,LEAD FREE



TE Part # 1-1761606-6
IDC LOW PRO HDR 60P VERT LA



TE Part # 3-1761606-6
IDC LOW PRO HDR 60P VERT LA



TE Part # 1-5103308-2
A/L LOW PRO HDR 60P VERT BLACK



Customers Also Bought



Documents

Product Drawings

060 STRAIN RELIEF A-L RCPT

English

CAD Files

Customer View Model

ENG_CVM_CVM_499252-7_AL.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_499252-7_AL.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_499252-7_AL.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ribbon Cable Interconnect Solutions](#)

English

Product Specifications

[Application Specification](#)

English