

402.6387**INTERLOCKED SOCKET**

63A 3P+N+E 6h 346-415V 60Hz 50Hz
170X380MM Screw terminals With
mechanical interlock



* Product image may be indicative



EN IEC 60309-1 (2022)

EN IEC 60309-2 (2022)

EN IEC 60309-4 (2022)

Low voltage direct. 2014/35/EU

■ GENERAL CHARACTERISTICS

Commercial Series	ADVANCE GRP Series
Synthetical description	INTERLOCKED SOCKET
Mounting version	FLUSH MOUNTING

■ TECHNICAL CHARACTERISTICS

Rated current	63A
Poles	3P+N+E
Hour position	6h
Rated voltage	346-415V
Working frequency	60Hz
	50Hz
Terminals	Screw terminals

■ PHYSICAL CHARACTERISTICS

Mounting version	FLUSH MOUNTING
Colour	RED
Material	GRP Glass Reinforced Polyester
Protection degree	Watertight
Protection degree IP	IP66/IP67/IP69
Protection degree IK	IK11(-40°C)
Contact material	CuZn (brass)
Working temperature	-40°C/+60°C
GLOW WIRE	GW 960°C
Self-extinguishing UL94	V0
Padlock	ø6,3mm

■ DIMENSIONAL CHARACTERISTICS

Flange	170X380MM
--------	-----------

■ DOWNLOAD

Technical drawing [PDF]
Technical drawing [STP]
Technical drawing [DWG]
Instruction manual

■ OPTIONS & VARIOUS NOTES

Options	With mechanical interlock
Notes	WITHOUT FUSE HOLDER
Catalogue notes	Supplied with stainless steel fixing screws.
	Empty base: ADVANCE-GRP System (fam. 579)