

Abrasive fibre disc, multibond

FS 966 ACT







Properties

Bonding agent	Resin
Grain	Ceramic Al. oxide
Coating	Close

Materials

Stainless steel	●

Product benefit

Micro-crystalline self-sharpening effect - High aggressiveness throughout the service life - Outstanding grit adhesion - Long service life, especially suitable for heavy-duty applications - Increase in performance due to low temperatures - Multibond prevents heat tinting

Applications

- Stainless steel processing industry
- Apparatus and container manufacturing

Available grits:

16 20 24 30 36 40 50 60 80 100 120 150 180 220 240 280 320 360 400 500 600 800 1000 1200 1500 2000 2500 3000

Diameter x Hole	Hole pattern	grain	Vmax m/s	Max. RPM	type of coat.abras.	bore shape	Article number
4-1/2 x 7/8 X-LOCK	⊛ 50	80	80 m/s	13300 rpm	FS 966	X-LOCK	351165
4-1/2 x 7/8 X-LOCK	⊛ 50	40	80 m/s	13300 rpm	FS 966	X-LOCK	351166
4-1/2 x 7/8 X-LOCK	⊛ 50	60	80 m/s	13300 rpm	FS 966	X-LOCK	351167
4-1/2 x 7/8	⊛ 30	36	80 m/s	13300 rpm	FS 966	star shaped hole	316490
4-1/2 x 7/8	⊛ 30	40	80 m/s	13300 rpm	FS 966	star shaped hole	316491
4-1/2 x 7/8	⊛ 30	60	80 m/s	13300 rpm	FS 966	star shaped hole	316492

Klingspor Schleifsysteme GmbH und Co. KG
Hüttenstraße 36 - 35708 Haiger - Germany
Fon + 49 (0) 2773 922-0 Fax + 49 (0) 2773 922-186
sales@klingspor.de - www.klingspor.de

Diameter x Hole	Hole pattern	grain	Vmax m/s	Max. RPM	type of coat.abras.	bore shape	Article number
4-1/2 x 7/8	⊛ 30	80	80 m/s	13300 rpm	FS 966	star shaped hole	316493
4-1/2 x 7/8	⊛ 30	50	80 m/s	13300 rpm	FS 966	star shaped hole	318504
4-1/2 x 7/8	⊛ 30	24	80 m/s	13300 rpm	FS 966	star shaped hole	318532
4-1/2 x 7/8	⊛ 30	120	80 m/s	13300 rpm	FS 966	star shaped hole	324237
5 x 7/8 X-LOCK	⊛ 50	80	80 m/s	12250 rpm	FS 966	X-LOCK	351162
5 x 7/8 X-LOCK	⊛ 50	60	80 m/s	12250 rpm	FS 966	X-LOCK	351163
5 x 7/8 X-LOCK	⊛ 50	40	80 m/s	12250 rpm	FS 966	X-LOCK	351164
5 x 7/8	⊛ 30	36	80 m/s	12250 rpm	FS 966	star shaped hole	316494
5 x 7/8	⊛ 30	40	80 m/s	12250 rpm	FS 966	star shaped hole	316495
5 x 7/8	⊛ 30	60	80 m/s	12250 rpm	FS 966	star shaped hole	316496
5 x 7/8	⊛ 30	80	80 m/s	12250 rpm	FS 966	star shaped hole	316497
5 x 7/8	⊛ 30	24	80 m/s	12250 rpm	FS 966	star shaped hole	318305
5 x 7/8	⊛ 30	120	80 m/s	12250 rpm	FS 966	star shaped hole	324239
7 x 7/8	⊛ 30	36	80 m/s	8500 rpm	FS 966	star shaped hole	316498
7 x 7/8	⊛ 30	40	80 m/s	8500 rpm	FS 966	star shaped hole	316499
7 x 7/8	⊛ 30	60	80 m/s	8500 rpm	FS 966	star shaped hole	316501
7 x 7/8	⊛ 30	80	80 m/s	8500 rpm	FS 966	star shaped hole	316502
7 x 7/8	⊛ 30	24	80 m/s	8500 rpm	FS 966	star shaped hole	318352
7 x 7/8	⊛ 30	120	80 m/s	8500 rpm	FS 966	star shaped hole	324238

Klingspor Schleifsysteme GmbH und Co. KG
Hüttenstraße 36 - 35708 Haiger - Germany
Fon + 49 (0) 2773 922-0 Fax + 49 (0) 2773 922-186
sales@klingspor.de - www.klingspor.de