



Cut



Medium Duty

## Economical solution for medium duty applications requiring very high cut resistance, grip & oil-repellence performance in oily environment

- **Heightened grip:** Featuring a fully NBR-coated seamless liner with a rough palm, EDGE<sup>®</sup> 48-969 protective gloves offer a highly secure grip in oily environments, while protecting skin from injuries and oil contamination
- **Optimized visibility:** these bright yellow cut-resistant gloves ensure that hands remain highly visible, promoting safety even in low-light or dark conditions
- **Enhanced defenses:** EDGE<sup>®</sup> 48-969 offers a high level of abrasion resistance and very high cut protection. In addition, the glove provides EN 407 level 1 contact heat protection, making it ideal for workers handling hot equipment, parts and objects.



### Industries

- Aerospace
- Automotive
- Glass manufacturing
- Machinery and Equipment
- Metal fabrication
- Transportation
- Energy

### Applications

- Machining / Stamping / Cutting
- Grinding
- Assembly of parts
- Maintenance
- Handling of glass sheets, sharp edged objects
- Handling materials with sharp or rough edges
- Handling sharp metal or objects

#### Key Features

- **NBR coating finish:** High grip in oily environment
- **Optimized visibility:** Bright yellow ensures high visibility
- **Thermal resistance:** Ability to confidently handle hot components

#### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN 407



X1XXXX

EN388: 2016



4X42F

#### Specifications

| BRAND   STYLE | DESCRIPTION                                                                                                                                                                        | Gauge | SIZE               | LENGTH                              | COATING COLOR    | PACKAGE                      |
|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------|-------------------------------------|------------------|------------------------------|
| EDGE® 48-969  | <b>Finishing:</b> Fully Dipped, Palm Coated, Rough<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> HPPE, Spandex, Nylon, Steel fiber<br><b>Cuff Style:</b> Knitwrist | 13    | 6, 7, 8, 9, 10, 11 | 225 to 275mm / 8.85 to 10.82 inches | Yellow and Black | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.