

VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester



1466612

<https://www.phoenixcontact.com/gb/products/1466612>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in surge protective device, in accordance with type 2/class II, for 1-phase power supply networks with separate N and PE (2-conductor system: N, PE).

Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

Commercial data

Item number	1466612
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL1381
Product key	CL1381
GTIN	4063151860219
Weight per piece (including packing)	130.65 g
Weight per piece (excluding packing)	108.4 g
Customs tariff number	85363030
Country of origin	DE

VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester



1466612

<https://www.phoenixcontact.com/gb/products/1466612>

Technical data

Product properties

Product type	Surge arrester
Product family	VAL-SPP
IEC test classification	II T2
EN type	T2
IEC power supply system	TN TT
Type	DIN rail module, two-section, divisible
Number of positions	1
Surge protection fault message	optical, remote signaling via optional module

Insulation characteristics

Overvoltage category	III
Pollution degree	3

Electrical properties

Maximum power dissipation for nominal condition	≤ 1.5 mVA
Nominal frequency f_N	50 Hz (60 Hz)

Connection data


Connection method	Screw connection
Screw thread	M5
Tightening torque	3 Nm ... 3.5 Nm
Stripping length	18 mm
Conductor cross-section flexible	1.5 mm ² ... 35 mm ² (without ferrule) 2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Conductor cross-section rigid	1.5 mm ² ... 50 mm ² 2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Conductor cross-section AWG	15 ... 2
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 16 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	1.5 mm ² ... 35 mm ² 2x 1.5 mm ² ... 10 mm ² (2 conductors with the same cross-section)
Conductor cross-section flexible, with ferrule without plastic sleeve	1.5 mm ² ... 25 mm ² 2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Connection method	Fork-type cable lug
Conductor cross-section flexible	1.5 mm ² ... 25 mm ²

VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester

1466612

<https://www.phoenixcontact.com/gb/products/1466612>

Dimensions

Dimensional drawing	
Width	17.8 mm
Height	96.6 mm
Depth	71.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	1 Div.

Material specifications

Color	gray (RAL 7042) light gray (RAL 7035)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6-FR 20 % GF PBT
Material group	I
Housing material	PA 6.6-FR 20 % GF PBT

Protective circuit

Mode of protection	N-PE
Direction of action	N-PE
Nominal voltage U_N	240 V AC $\pm 10\%$ (TN - only N-PE) 240 V AC $\pm 10\%$ (TT - only N-PE)
Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous operating voltage U_C	305 V AC
Protective conductor current I_{PE}	$\leq 5 \mu A$
Nominal discharge current I_n (8/20) μs	20 kA
Maximum discharge current I_{max} (8/20) μs	40 kA
Follow current interrupt rating I_{fi}	100 A
Voltage protection level U_p	≤ 1.5 kV
Residual voltage U_{res}	≤ 0.5 kV (at I_n) ≤ 0.4 kV (at 10 kA) ≤ 0.3 kV (at 5 kA) ≤ 0.1 kV (at 3 kA)
Front-of-wave sparkover voltage at 6 kV (1.2/50) μs	≤ 1.5 kV
TOV behavior at U_T	1200 V AC (200 ms / withstand mode)
Response time t_A	≤ 100 ns

Environmental and real-life conditions

VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester



1466612

<https://www.phoenixcontact.com/gb/products/1466612>

Ambient conditions

Degree of protection	IP20C (Installed)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	≤ 5000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x ±X, ±Y, ±Z)
Vibration (operation)	5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012 + A11:2018

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester




1466612



<https://www.phoenixcontact.com/gb/products/1466612>

Drawings

Dimensional drawing




Schematic diagram

Pollution degree	2		3	
	Altitude		Altitude	
	≤4000 m	5000 m	≤4000 m	5000 m
 ≥50 mm ²	-	-	-	-
 ≥35 mm ²	-	-	-	-
 ≥25 mm ²	-	-	-	-
 ≥16 mm ²	-	1 mm	1 mm	1 mm

Minimum lateral distance to active and grounded conductive parts

1466612

<https://www.phoenixcontact.com/gb/products/1466612>



Max. permissible current in relation to the ambient temperature

VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester



1466612

<https://www.phoenixcontact.com/gb/products/1466612>

Circuit diagram



VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester



1466612

<https://www.phoenixcontact.com/gb/products/1466612>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1466612>

DNV

Approval ID: TAE0000501



IECEE CB Scheme

Approval ID: NL-118261

VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester



1466612

<https://www.phoenixcontact.com/gb/products/1466612>

Classifications

ECLASS

ECLASS-13.0	27171202
ECLASS-15.0	27171202

ETIM

ETIM 9.0	EC000941
----------	----------

VAL-SPP-T2-NPE-0+1-UT - Type 2 surge arrester



1466612

<https://www.phoenixcontact.com/gb/products/1466612>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk