



Main

Range of product	Ovalis C Series
Product or component type	Data socket
Device presentation	Mechanism with fixing frame
Data socket type	RJ45 8 contact(s) Cat.6 <= 250 MHz
Type of packing	Paint cover
Sale per indivisible quantity	1
Condition of use	Indoor

Complementary






Device mounting	Flush
Socket number	1
Organization of wire	Shielded twisted pair
Cable shielding type	STP
Product compatibility	S-one connector
Fixing mode	By screws
Colour tint	White (RAL 9003)
Surface finish	Matt
Surface treatment	Antibacterial
Provided equipment	Supplied with claws
Connections - terminals	IDC
Number of loop terminals	1
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	71 mm
Width	71 mm
Depth	41.7 mm
Embedding depth	25.7 mm
Net weight	0.095 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	IEC 60603-7 IEC 60603-7-5 ANSI/TIA/EIA-568-B-2-1 TIA/EIA-568 ISO/IEC 11801 EN 50173-1 ANSI/TIA/EIA-568-B-2
IP degree of protection	IP21
IK degree of protection	IK04
Environmental characteristic	Bleach Liquid soap Window-cleaning fluid Alcohol Acetone Oil UV resistant Petrol

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations