




Wire Protection & Management > Heat Shrink Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**
Number of Branches & Legs: **3**
Material Code: **71**
Material Systems Code: **10**
Adhesive Requirement: **Adhesive Precoat**

Features

Product Type Features

Molded Part Shape	Y Shape
-------------------	---------

Configuration Features

Number of Branches & Legs	3
Adhesive Requirement	Adhesive Precoat

Body Features

Primary Product Material	Semi-Rigid Modified Polyolefin
Material Code	71
Material Systems Code	10

Dimensions

Inside Diameter Range (Leg 2)	6.6 – 13.2 mm[.26 – .52 in]
Inside Diameter Range (Leg 1)	6.6 – 13.2 mm[.26 – .52 in]
Inside Diameter Range (Body)	6.6 – 19.8 mm[.26 – .78 in]

Usage Conditions

Flammability Performance	Flame-Retardant
Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
Resistance Protection	Long-Term Fluid Exposure at High Temperatures



Operation/Application

Mechanical Resistance	Flexing
-----------------------	---------

Other

Molded Part Shape Code	381A
Size Code	301
Adhesive Code	180

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 9-120035-5

[HarnWare/HarnVis Purchase Charge](#)



TE Part # 9-120035-6

[HarnWare/HarnVis Renewal Charge](#)

Customers Also Bought



TE Part #2-1747276-2

[DYNAMIC D4200 REC HSG 2P/Y](#)



TE Part #462006-1

[FLOATING SHEAR](#)



TE Part #804527-000

[55PC1121-22-2/6-9CS2502](#)




TE Part #1-175196-2

[DYNAMIC D-3 REC CONT/L AU 0.38](#)



TE Part #2-1318116-3

[DYNAMIC D2100 TAB HSG 3P P/M Y](#)




TE Part #CAT-R21-731072

[Bulbous Heat Shrink Boots: Lipped, Straight](#)




TE Part #1-1903130-3

[DYNAMIC 1200D TAB HSG 6P F/H](#)



TE Part #763665J001

[V2-25.0-0-FSP-SM](#)



TE Part #5038604008

[DCPT-6/3-45-SP](#)

Documents

Product Drawings

[381A301-71/180-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-71](#)

English

[Raychem Molded Parts Visual Guide](#)

English



Product Specifications

Product Specification

English