## Product data sheet Characteristics

## TM5SDO2T

digital output module - 20 - 24V DC - 0,5A - 3 wires



#### Main

Range of product	Modicon TM5		
Product or component type	Discrete output module		
Discrete output number	2		
Discrete output type	Transistor		

#### Complementary

Range compatibility	Modicon LMC058 Modicon M258			
Product compatibility	Motion controller Logic controller			
Output voltage	24 V DC			
Output voltage limits	20.428.8 V			
Discrete output logic	Source			
Current per channel	0.5 A			
Current per output common	<= 1 A			
Colour	White			
Peak output current	<= 12 A			
Switching frequency	<= 500 Hz resistive load			
Response time	<= 300 µs from state 1 to state 0 for output <= 300 µs from state 0 to state 1 for output			
Leakage current	5 μA when switched off			
Short-circuit protection	With			
Overload protection	With			
Reverse polarity protection	With			
Voltage drop	<= 2 V at 500 mA for sensor supply <= 0.3 V at 500 mA for output			
Supply current for sensors	500 mA			
Current consumption	26 mA 5 V DC bus 14 mA 24 V DC input/output			
Power dissipation in W	<= 0.57 W			
Local signalling	2 LEDs yellow for output status 1 LED red for power supply 1 LED green for power supply			
Electrical connection	3 wires			
Marking	CE			
Product weight	0.025 kg			

#### **Environment**

Liviloiiiioiit				
Standards	CSA 22-2 No 142 IEC 61131-2 UL 508 CSA 22-2 No 213			
Product certifications	CSA C-Tick CULus GOST-R			
Ambient air temperature for operation	060 °C with derating factorhorizontal installation 055 °C without derating factorhorizontal installation 050 °C vertical installation			
Ambient air temperature for storage	-2570 °C			
Relative humidity	595 % without condensation			
IP degree of protection	IP20 conforming to IEC 61131-2			
Pollution degree	2 conforming to IEC 60664			
Operating altitude	02000 m			
Storage altitude	03000 m			
Vibration resistance	3.5 mm 58.4 Hz DIN rail 1 gn 8.4150 Hz DIN rail			
Shock resistance	15 gn for 11 ms			
Resistance to electrostatic discharge	8 kV in air conforming to EN/IEC 61000-4-2 4 kV on contact conforming to EN/IEC 61000-4-2			
Resistance to electromagnetic fields	10 V/m 802000 MHz conforming to EN/IEC 61000-4-3 1 V/m 22.7 GHz conforming to EN/IEC 61000-4-3			
Resistance to fast transients	2 kV power lines conforming to EN/IEC 61000-4-4 1 kV shielded cable conforming to EN/IEC 61000-4-4 1 kV I/O conforming to EN/IEC 61000-4-4			
Surge withstand	1 kV common mode conforming to EN/IEC 61000-4-5 0.5 kV differential mode conforming to EN/IEC 61000-4-5			
Electromagnetic compatibility	EN/IEC 61000-4-6			
Disturbance radiated/conducted	CISPR11			

#### Not classified

Isolation	No insulation between channels
	500 Vrms AC insulation between channel and bus

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 1039 - Schneider Electric declaration of conformity download declaration of conformity




# Product data sheet Dimensions Drawings

# TM5SDO2T

#### TM5 Slice


#### Dimensions




# TM5SDO2T


#### TM5 System

#### Spacing Requirements





#### Mounting on a DIN Rail



## TM5SDO2T


#### TM5 System Wiring Recommendations

#### Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in.	0.35	<u> </u>	1		
	mm²	0,082,5	0,252,5	0,251,5	2 x 0,252 x 0,75
	AWG	2814	24 14	2416	2 x 242 x 18

#### Electronic Module 2DO 24 Vdc Tr 0.5 A 3 Wires

#### Wiring Diagram



- Internal electronics (1)
- 24 Vdc I/O power segment integrated into the bus bases (2)
- (3) Inductive load protection
- 2-wire load
- 3-wire load