


- ***Small footprint***
- ***4 actuation forces***
- ***Excellent tactile feel***
- ***Ultra low current capabilities***
- ***IP40***

- **Automotive**
- **Industrial electronics**
- **Medical equipment**



FUNCTION: momentary action
CONTACT ARRANGEMENT: 1 make contact = SPST, N.O.
TERMINALS: Gullwing type for SMT

Type G and NG See description below	Operating force N (grs)	Operating life (cycles)	Travel (mm)
KMR211 LFS	1.2 (120) $\pm$ 0.30	200,000	0.20 mm $\pm$ 0.1
KMR211 ULC LFS	1.2 (120) $\pm$ 0.30	200,000	0.20 mm $\pm$ 0.1
KMR213 LFG	1.2 (120) $\pm$ 0.30	200,000	0.20 mm $\pm$ 0.1
KMR213 ULC LFG	1.2 (120) $\pm$ 0.30	200,000	0.20 mm $\pm$ 0.1
KMR221 LFS	2.0 (200) $\pm$ 0.50	200,000	0.25 mm $\pm$ 0.1
KMR221 ULC LFS	2.0 (200) $\pm$ 0.50	200,000	0.25 mm $\pm$ 0.1
KMR223 LFG	2.0 (200) $\pm$ 0.50	200,000	0.25 mm $\pm$ 0.1
KMR223 ULC LFG	2.0 (200) $\pm$ 0.50	200,000	0.25 mm $\pm$ 0.1
KMR231 LFS	3.0 (300) $\pm$ 0.75	150,000	0.25 mm $\pm$ 0.1
KMR231 ULC LFS	3.0 (300) $\pm$ 0.75	150,000	0.25 mm $\pm$ 0.1
KMR232 LFS	3.0 (300) $\pm$ 0.75	300,000	0.25 mm $\pm$ 0.1
KMR232 ULC LFS	3.0 (300) $\pm$ 0.75	300,000	0.25 mm $\pm$ 0.1
KMR233 LFG	3.0 (300) $\pm$ 0.75	150,000	0.25 mm $\pm$ 0.1
KMR233 ULC LFG	3.0 (300) $\pm$ 0.75	150,000	0.25 mm $\pm$ 0.1
KMR241 LFS	4.0 (400) $\pm$ 1.00	100,000	0.30 mm $\pm$ 0.1
KMR241 ULC LFS	4.0 (400) $\pm$ 1.00	100,000	0.30 mm $\pm$ 0.1
KMR242 LFS	4.0 (400) $\pm$ 1.00	200,000	0.30 mm $\pm$ 0.1
KMR242 ULC LFS	4.0 (400) $\pm$ 1.00	200,000	0.30 mm $\pm$ 0.1
KMR243 LFG	4.0 (400) $\pm$ 1.00	100,000	0.30 mm $\pm$ 0.1
KMR243 ULC LFG	4.0 (400) $\pm$ 1.00	100,000	0.30 mm $\pm$ 0.1

Electrical	Silver	Gold
MAXIMUM POWER:	1 VA	0.2 VA
MAXIMUM VOLTAGE:	32 VDC	32 VDC
MINIMUM VOLTAGE:	20 mVDC	20 mVDC
MAXIMUM CURRENT:	50 mA	10 mA
MINIMUM CURRENT:	1 mA*	1 mA*
DIELECTRIC STRENGTH:	≥ 250 Vrms	
CONTACT RESISTANCE:	≤ 100 mΩ	
INSULATION RESISTANCE:	≥ 1GΩ	
BOUNCE TIME:	≤ 3 ms	

*For ULC version minimum current is 1μA at 1.8 VDC

Environmental	Silver	Gold
OPERATING TEMPERATURE:	-40°C to 85°C	-40°C to 125°C
STORAGE TEMPERATURE:	-55°C to 85°C	-55°C to 125°C


Infrared Reflow Soldering in accordance with IEC61760-1

In reels of 7,000 pieces
External diameter 330 mm $\pm$ 2 mm

NOTE: Specifications listed above are for switches with standard options.
For information on specific and custom switches, consult Customer Service Center.

TACTILE FEELING: KMR 2 series with actuation force in 2N - 3N - 4N: $\geq 30\%$
KMB 2 series with actuation force in 1.2N: $\geq 20\%$

For any part number different from those listed above, please consult your local representative.



* Silver long life is available in 3N and 4N actuation force. For other versions, please contact Customer Service.

Dimensions are shown: mm
Specifications and dimensions subject to change

KMR 2 Series Microminiature Tact Switch for SMT


KMR 2 Series - 1.9 mm height

PCB layout shown with ground pin option




B

Tactile Switches



TAPE & REEL



First Angle
Projection

Dimensions are shown: mm
Specifications and dimensions subject to change



8 jun 16

B-12

www.ck-components.com