

Technical data


2307SC3

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	35 mm
D - External diameter	80 mm
B - Bearing/Inner ring width	31 mm
rs - Min fillet radius	1,5 mm
Radial clearance class	C3
Precision class	P0
Mass	0,671 kg

PRODUCT PERFORMANCE

C - Dynamic load	40000000 mN
C0 - Static load	11300000 mN
Cu - Fatigue limit load	480000 mN
e - Coefficient	0.46
Y0 - Static axial load coefficient	1.4
Y1 - Lower axial load coefficient	1.4
Y2 - Upper axial load coefficient	2.1
N lim - Oil lubrication limit speed	54000 °/s
N lim - Grease lubrication limit speed	42600 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	43 mm
Da max - Max shoulder diameter OR	72 mm



ABUTMENT	
ra max - Max shaft & housing fillet radius	1,5 mm