



CE
EN ISO 21420



EN 388

2122X



EN 407

41314X

EN 12477
TYPE
B



EU regulation 2016/425 attest n°0075/057/162/12/23/2031 delivered by CTC, notified body n°0075

SOFTWELDER

WELDING GLOVES



PPE Category II

	EN388:2016 +A1:2018
Resistance to abrasion : Blade cut resistance : Tear resistance : Puncture resistance : Blade Cut resistance according to ISO13997 :	Levels : ●●○○ ●○○○○ ●●○○ ●●○○ X
	EN407:2020
Burning behaviour : Contact heat : Convective heat : Radiant heat : Small splashes of molten metal : Large splashes of molten metal :	Levels : ●●●● ●○○○ ●●○○ ●○○○ ●●●● X
Sizes	Packaging
6 - 7 - 8 - 9 - 10 - 11 - 12	12 per packet - 72 per box

Extra flexible goat grain leather glove for a maximum comfort, "fourchettes" assembling for a better durability and an improved ergonomics to reach optimal dexterity for TIG welding applications for example. 15 cm soft black cow split leather cuff. 100% para-aramid sewing thread.

THE + PRODUCT



SOFTNESS



DEXTERITY



COMFORT

RELEVANT SECTORS



Automotive
manufacturing and
supply industry



Engineering industry
and Industrial
maintenance



Metal manufacturing
and processing
industry



Welding works

RANGE



POWERWELD



LEBON International S.à.r.l
Immeuble Laccollith
20, rue Eugène Ruppert L-2453 Luxembourg
Website : www.lebonprotection.com
TEL : +352 26 49 36 07
FAX : +352 26 49 35 35