

Main

Range	New Unica
Device application	Signalling
Product or component type	Buzzer
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
[Ue] rated operational voltage	230 V AC 50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)

Complementary

Current consumption	40 mA
Type of setting	Volume can be adjusted using a screw
Device mounting	Flush
Operating time	<= 30 ms
Connections - terminals	Screw terminals
Acoustic level	Between 76 and 80 dB
Cable cross section	0.75...1.5 Mm ² flexible cable 0.75...1.5 mm ² rigid cable
Material	Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing
Standards	EN 62080 CE
Directives	2014/35/EU - low voltage directive
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	31 mm
Depth	50 mm
Width	45 mm
Height	45 mm
Net weight	0.091 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
IP degree of protection	IP20

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins