

12v Max CXT Drill Driver

DF333D

Capacity in Steel	10mm
Capacity in Wood	21mm
Chuck Capacity	0.8mm – 10mm
No Load Speed	Low: 0- 450rpm Hi: 0- 1,700rpm
Torque Settings	20 + Drill
Max Tightening Torque	Soft: 14Nm Hard: 30Nm
Net Weight	1.1-1.2kg

Body only machines do not come with a carry case.



DF333DWAE 2 x 2.0Ah Li-ion

DF333DZ Body Only

STANDARD EQUIPMENT: Standard charger, battery cartridges, screwdriver bit, carry case.



CXT
LITHIUM-ION

