




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.31 – 3.31 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Locking Lance

Dimensions

Product Length	21.46 mm
Compatible Insulation Diameter Range	3.81 – 4.83 mm[.15 – .19 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	1.31 – 3.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	8000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



KIT

REPRESENTATION ONLY

TE Part # 7-2150872-7
[OCEAN_2.0_SPARE_PART_KIT-120F210F](#)




TE Part # 42663-2
[FF 312 REC 16-12AWG TPBR](#)



TE Part # 2150872-2
[OCEAN_2.0_APPLICATOR-E-120F210F-REA](#)

Also in the Series | **FASTIN-FASTON 250**



[Crimp Terminal Housings\(195\)](#)



[Insertion & Extraction Tools\(2\)](#)



[Quick Disconnects\(216\)](#)


Customers Also Bought




TE Part #1-2328352-2
[25POS, MIXED,REC HSG,ASSY, SEALED, COD A](#)




TE Part #2-1437719-1
[T01-0550-P05-MALE PLUG CONNECTOR SOLDER](#)



TE Part #776087-1
[23POS,PIN DIA 1.3,HDR ASSY,90DEG, COD 1](#)




TE Part #1-174258-1
[E-J MK-2 PLUG HSG 4P NATURAL COD 1](#)



TE Part #874333-000
[202K142-100/180-0](#)



TE Part #HDP26-24-31PE-L015
[PLG, 31P, BLK, E, THD, 16, P](#)



TE Part #282180-3
[FF 187 REC 0.5-1.5MM2 TPPB](#)



TE Part #1-2344950-1
[95POS, HYBRID, REC HSG, ASSY, COD A](#)



TE Part #62505-1
[PIN 130 22-18 AWG .0157 X 1.020 BR](#)



TE Part #F77737-000
[HX-SCE-1K-4.8-50-9](#)

Documents

Product Drawings

[FF 250 REC TERMINAL 16-12 AWG TPBR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_42904-2_AY_c-42904-2-ay.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42904-2_AY_c-42904-2-ay.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42904-2_AY_c-42904-2-ay.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English