

# Protective hose fixing bracket - WP-BASE A M40 - 3241087

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fixing bracket for protective sleeves, fixed with two screws

Image shows WP-FB PG 21 version



## Key commercial data

Packing unit	25 pc
Minimum order quantity	25 pc
GTIN	 4 046356 712309
Weight per Piece (excluding packing)	66.45 g
Custom tariff number	73269098
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Dimensions

Hole diameter	43 mm
---------------	-------

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 200 °C
---------------------------------	-------------------

### General

Color	silver
Components	Halogen-free
Material	Steel, galvanized

## Classifications

### eCl@ss

eCl@ss 4.0	27141209
------------	----------

## Protective hose fixing bracket - WP-BASE A M40 - 3241087

### Classifications

#### eCl@ss

eCl@ss 4.1	27141209
eCl@ss 5.0	21132007
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

#### ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC002498
ETIM 5.0	EC002498

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411