

Article No. : 1FL2310-2AC01-1MB0



Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Basic motor data	
Motor type	Permanent-magnet synchronous motor
Motor type	High Inertia
Static torque	18.10 Nm
Static current	11.00 A
Maximum torque	55.00 Nm
Maximum current	36.2 A
Maximum speed	3,000 rpm
Rotor moment of inertia	69.0950 kgcm²
Weight	19.4 kg

Rated data	
SINAMICS S200, 3 AC 380 ... 480 V	
Rated speed	2,000 rpm
Rated torque	16.70 Nm
Rated current	11.0 A
Rated power	3.50 kW

Encoder system	
Encoder system	Absolute encoder 21-bit singleturn + 12-bit multiturn

Motor connection	
Connection type	Metal angular connector

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	90
Flange size (AB)	180 mm
Centering ring (N)	114.3 mm
Hole circle (M)	200 mm
Screw-on hole (S)	13.5 mm
Overall length (LB)	215.5 mm
Diameter of shaft (D)	35 mm
Length of shaft (E)	80 mm
Length of flange diagonal (P)	228 mm
Shaft end	Shaft with parallel key (half-key balancing)
Color of the housing	Anthracite RAL 7016

