

LOC		DIST		REVISIONS						
AD	00	P	LTR	DESCRIPTION				DATE	DWN	APVD
			—	SEE SHEET 1				—	—	—

9	7	64.01 [2.520]	66.04 [2.600]	24	25	7-103673-4	OBSOLETE	10
9	7	61.47 [2.420]	63.50 [2.500]	23	24	7-103673-3		
9	7	58.93 [2.320]	60.96 [2.400]	22	23	7-103673-2	OBSOLETE	10
9	7	56.39 [2.220]	58.42 [2.300]	21	22	7-103673-1	OBSOLETE	10
9	7	53.85 [2.120]	55.88 [2.200]	20	21	7-103673-0	OBSOLETE	10
9	7	51.31 [2.020]	53.34 [2.100]	19	20	6-103673-9		
9	7	48.77 [1.920]	50.80 [2.000]	18	19	6-103673-8	OBSOLETE	10
9	7	46.23 [1.820]	48.26 [1.900]	17	18	6-103673-7	OBSOLETE	10
9	7	43.69 [1.720]	45.72 [1.800]	16	17	6-103673-6		
9	7	41.15 [1.620]	43.18 [1.700]	15	16	6-103673-5		
9	7	38.61 [1.520]	40.64 [1.600]	14	15	6-103673-4		
9	7	36.07 [1.420]	38.10 [1.500]	13	14	6-103673-3		
9	7	33.53 [1.320]	35.56 [1.400]	12	13	6-103673-2	OBSOLETE	10
9	7	30.99 [1.220]	33.02 [1.300]	11	12	6-103673-1		
9	7	28.45 [1.120]	30.48 [1.200]	10	11	6-103673-0		
9	7	25.91 [1.020]	27.94 [1.100]	9	10	5-103673-9		
9	7	23.37 [.920]	25.40 [1.000]	8	9	5-103673-8		
9	7	20.83 [.820]	22.86 [.900]	7	8	5-103673-7		
9	7	18.29 [.720]	20.32 [.800]	6	7	5-103673-6		
9	7	15.75 [.620]	17.78 [.700]	5	6	5-103673-5		
9	7	13.21 [.520]	15.24 [.600]	4	5	5-103673-4		
9	7	10.67 [.420]	12.70 [.500]	3	4	5-103673-3		
9	7	8.13 [.320]	10.16 [.400]	2	3	5-103673-2		
9	7	5.59 [.220]	7.62 [.300]	1	2	5-103673-1		
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.		

8	7	41.15 [1.620]	43.18 [1.700]	15	16	2-103673-6		
8	7	18.29 [.720]	20.32 [.800]	6	7	2-103673-5		
1	1	64.01 [2.520]	66.04 [2.600]	24	25	2-103673-4		
1	1	61.47 [2.420]	63.50 [2.500]	23	24	2-103673-3		
1	1	58.93 [2.320]	60.96 [2.400]	22	23	2-103673-2	OBSOLETE	10
1	1	56.39 [2.220]	58.42 [2.300]	21	22	2-103673-1		
1	1	53.85 [2.120]	55.88 [2.200]	20	21	2-103673-0	OBSOLETE	10
1	1	51.31 [2.020]	53.34 [2.100]	19	20	1-103673-9		
1	1	48.77 [1.920]	50.80 [2.000]	18	19	1-103673-8	OBSOLETE	10
1	1	46.23 [1.820]	48.26 [1.900]	17	18	1-103673-7		
1	1	43.69 [1.720]	45.72 [1.800]	16	17	1-103673-6		
1	1	41.15 [1.620]	43.18 [1.700]	15	16	1-103673-5		
1	1	38.61 [1.520]	40.64 [1.600]	14	15	1-103673-4		
1	1	36.07 [1.420]	38.10 [1.500]	13	14	1-103673-3		
1	1	33.53 [1.320]	35.56 [1.400]	12	13	1-103673-2	OBSOLETE	10
1	1	30.99 [1.220]	33.02 [1.300]	11	12	1-103673-1		
1	1	28.45 [1.120]	30.48 [1.200]	10	11	1-103673-0		
1	1	25.91 [1.020]	27.94 [1.100]	9	10	103673-9		
1	1	23.37 [.920]	25.40 [1.000]	8	9	103673-8		
1	1	20.83 [.820]	22.86 [.900]	7	8	103673-7		
1	1	18.29 [.720]	20.32 [.800]	6	7	103673-6		
1	1	15.75 [.620]	17.78 [.700]	5	6	103673-5		
1	1	13.21 [.520]	15.24 [.600]	4	5	103673-4		
1	1	10.67 [.420]	12.70 [.500]	3	4	103673-3		
1	1	8.13 [.320]	10.16 [.400]	2	3	103673-2		
1	1	5.59 [.220]	7.62 [.300]	1	2	103673-1		
PLATING	C	B	A	NO. OF POSN	PART NO.			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

± -
± -
± -
± -
± -
± -

TOLERANCES, UNLESS
OTHERWISE SPECIFIED:

± 0.13[.005]

MATERIAL

-

FINISH

SEE TABLE

DWN
S. SHUEY

CHK
J. GESFORD

APVD
J. GESFORD

OSMAR91

OSMAR91

OSMAR91

NAME

HDR ASSY, RTANG, SINGLE ROW
2.54[.100] C/L 0.641[.025] SQ. POST,
WITH PLZN & HOLD DOWNS, AMPMODU MTE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

108-25034

114-25026

100779

103673

4:1

2

2

13

CUSTOMER DRAWING

SCALE

SHEET

OF

REV