

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Impact Driver/Wrench

PRO GDX 18V-285



The ideal tool for bolting and screwdriving with one tool holder

The most important data

Battery voltage	18.0 V
Torque, max.	285 Nm
No-load speed	0-2,800 rpm

Part Number 0 601 9N2 120

Technical data

Technical data

Torque adjustment range, min./max., 1st level	0/200 Nm
Torque adjustment range, min./max., 2nd level	0/285 Nm
No-load speed	0-2,800 rpm
No-load speed (1st level)	0-2,000 rpm
No-load speed (2nd level)	0-2,800 rpm
Torque settings	2
Weight excl. battery	1.1 kg
Torque, max.	285 Nm
Impact rate	0-3,600 bpm
Impact rate (1st level)	0-3,000 bpm
Impact rate (2nd level)	0-3,600 bpm
Battery voltage	18.0 V
Tool holder	1/2" square friction ring and thru hole, 1/4" Hex Uni
Breakaway torque, max.	500 Nm
Packaging dimensions (width x length x height)	73 x 147 x 210 mm
Weight incl. battery	1.13 kg

Noise/vibration information

Tightening screws and nuts of maximum permitted size

Vibration emission value ah	15.8 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- Convenient and saves time with single tool, GDx 2-in-1 tool holder for both screw-driving and bolting application
- Powerful bolting tool with 285 Nm torque performs bolting applications with ease
- 2-Speed Selector
- High speed for productivity, medium for delicate jobs
- Comfortable to use for long periods thanks to the ergonomic handle with Soft-grip and slim handle



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

