



Product: [8471NH](#)

Electronic, 2 C #16 Str TC, LSZH Ins, LSZH Jkt

[Request Sample](#)

Product Description

Electronic, 2 Conductor 16AWG (19x29) Tinned Copper, LSZH Insulation, LSZH Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details

Conductor

Size	Stranding	Material
16	19x29	TC - Tinned Copper

Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
LSZH - Low Smoke Zero Halogen (Flame Retardant)	2.67 mm (0.105 in)	Black & White	Flame Retardant

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.89 mm (0.035 in)	7.1 mm (0.28 in)

Overall Cable Diameter (Nominal):	7.1 mm (0.28 in)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
14.7 Ohm/km (4.48 Ohm/1000ft)	52 pF/m (16 pF/ft)	7.1 Amps per Conductor

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-20°C To +75°C	-15°C To +80°C	-45°C To +80°C

Bend Radius

Installation Min.
71 mm (2.8 in)

Max. Pull Tension:	127 N (28.6 lbf)
Bulk Cable Weight:	32 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Dca, Indoor, Non-Halogenated, Sunlight Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-24
CPR Compliance:	CPR Euroclass: Dca-s1,d1,a1; CPR UKCA Class: Dca-s1,d1,a1
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 60%
CENELEC Compliance:	EN 50290-2-20
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.391 Revision Date: 12-02-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
8471NH.01500	Blue	Reel	500 m	8719605018359
8471NH.00152	Chrome	Reel	152 m	8719605018328
8471NH.00305	Chrome	Reel	305 m	8719605018335
8471NH.00500	Chrome	Reel	500 m	8719605018342
8471NH.001000	Chrome	Reel	1,000 m	8719605018304
8471NH.001500	Chrome	Reel	1,500 m	8719605018311
8471NH.021000	Green	Reel	1,000 m	8719605148087
8471NH.03305	White	Reel	305 m	8719605197290
8471NH.03500	White	Reel	500 m	8719605161666
8471NH.031000	White	Reel	1,000 m	8719605161680

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.