




AMP

TE Internal #: 1355968-1

Contact Extraction, Contact-to-Housing, Insertion & Extraction Tools

[View on TE.com >](#)

Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2236905-4
NANO TAB 0.5X0.4,TERMINAL



TE Part # 2302461-9
MATENET INLINE COUPLER, ASSY, COD Z



TE Part # 2362347-3
MATENET, F INSERT TO F INSERT, 1500MM



TE Part # 2362347-1
MATENET, F INSERT TO F INSERT, 500MM



TE Part # 2362347-5
MATENET, F INSERT TO F INSERT, 5000MM



TE Part # 2302461-3
MATENET INLINE COUPLER, ASSY, COD C



TE Part # 2302461-1
MATENET INLINE COUPLER, ASSY, COD A



TE Part # 2302461-2
MATENET INLINE COUPLER, ASSY, COD B



TE Part # 2362347-4
MATENET, F INSERT TO F INSERT, 3000MM

Customers Also Bought



TE Part #1803095-7
FLOATING SHEAR, FRONT



TE Part #2-1333225-0
ANVIL, COMB., SPECIAL



TE Part #6-1633620-7
ANVIL, COMBINATION



TE Part #9-1333225-0
ANVIL, COMBINATION



TE Part #2355843-1
1POS, COAX, SOC HSG ASSY, SLD

TE Part #1-1338690-2
ANVIL, COMBINATION .055

TE Part #1-562108-5
CRIMPER WIRE

TE Part #1-1338690-1
ANVIL, COMBINATION .055

TE Part #2-1490019-3
CRIMPER, WIRE (.050" 'F')

TE Part #2234991-1
HEATING ELEMENT ASSEMBLY

Documents

Product Drawings
EXTRACTION TOOL
English

Datasheets & Catalog Pages
CRIMPING TERMINALS
English
CRIMPING WHERE FORM MEETS FUNCTION
English