


Fluidic muscle DMSP-20-100N-RM-CM

Part number: 8114534

FESTO



 General operating condition

Data sheet

Feature	Value
Size	20
Diameter increase with max. contraction	40 mm
Stroke	0 mm ... 2250 mm
Max. contraction	25% of nominal length
Max. initial tension	4% of nominal length
Nominal length	100 mm
Repetition accuracy muscle	$\leq 1\%$ of nominal length, cyclical
Permissible parallelism tolerance	$\pm 0.5\%$ up to nominal length of 400 mm
Permissible angle tolerance	≤ 1 deg
Mounting position	optional
Design	Contracting diaphragm
Symbol	00991121
Operating pressure	0 MPa ... 0.6 MPa
Operating pressure	0 bar ... 6 bar
Mode of operation	Single-acting Pulling
Approval	German Technical Control Board (TÜV)
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-5 °C ... 60 °C
Max. working load freely suspended	80 kg
Theoretical Fluidic Muscle force at max. operating pressure	1500 N
Theoretical force at 0.6 MPa (6 bar, 87 psi)	1500 N
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material flange	Wrought aluminium alloy Colourless anodised
Material sleeve	Wrought aluminium alloy Colourless anodised
Material membrane	AR Chloroprene rubber
Material nut	Steel Galvanised