

SPECIFICATIONS

Model		RH-12A
Rated Voltage		12V DC
Operating Voltage		9V to 16V DC
Current Consumption		800mA
	Buzzer	
Power Consumption		9.6W
Flashing Rate		170 Flashes Per Minute
Operating Temperature Range (Relative Humidity)		- 30°C to + 80°C (Less than 90%)
Mounting	Location	Indoor & Outdoor Use
	Direction	Indoor: Upright, Inverted & Sideways Outdoor: Upright Only
Protection Rating		IP23 (IP55 with optional rubber gasket SZ-200A)
Vibration Resistance		70.0m/s ² (33Hz, Back and Forth:2h • Right to Left:2h • Up and Down:2h)
Insulation Resistance		
Withstanding Voltage		
Buzzer	Sound Level	
	Tone	
Bulb	Rating	12V 10W
	Base/Bulb	BA15S / G18
Luminous Intensity		8000cd or more without dome
Mass (Tolerance ±10%)		0.4kg

No.RH-12A-PDFF-EN-1_2

- This product conforms to the CE requirements and shows the CE Marking.

PATLITE Corporation

SPECIFICATIONS

Model		RH-24A
Rated Voltage		24V DC
Operating Voltage		20V to 30V DC
Current Consumption		500mA
	Buzzer	
Power Consumption		12.0W
Flashing Rate		170 Flashes Per Minute
Operating Temperature Range (Relative Humidity)		- 30°C to + 80°C (Less than 90%)
Mounting	Location	Indoor & Outdoor Use
	Direction	Indoor: Upright, Inverted & Sideways Outdoor: Upright Only
Protection Rating		IP23 (IP55 with optional rubber gasket SZ-200A)
Vibration Resistance		70.0m/s ² (33Hz, Back and Forth:2h • Right to Left:2h • Up and Down:2h)
Insulation Resistance		
Withstanding Voltage		
Buzzer	Sound Level	
	Tone	
Bulb	Rating	24V 10W
	Base/Bulb	BA15S / G18
Luminous Intensity		5200cd or more without dome
Mass (Tolerance ±10%)		0.4kg

No.RH-24A-PDFF-EN-1_2

- This product conforms to the CE requirements and shows the CE Marking.

PATLITE Corporation

SPECIFICATIONS

Model		RH-100A
Rated Voltage		100V AC (50/60Hz)
Operating Voltage		90V to 110V AC
Current Consumption		65mA
	Buzzer	
Power Consumption		6.2W
Flashing Rate		170 Flashes Per Minute
Operating Temperature Range (Relative Humidity)		- 30°C to + 60°C (Less than 90%)
Mounting	Location	Indoor & Outdoor Use
	Direction	Indoor: Upright, Inverted & Sideways Outdoor: Upright Only
Protection Rating		IP23 (IP55 with optional rubber gasket SZ-200A)
Vibration Resistance		45.0m/s ² (33Hz, Back and Forth:2h • Right to Left:2h • Up and Down:2h)
Insulation Resistance		More than 1MΩ at 500VDC between the terminals and the chassis
Withstanding Voltage		1000VAC applied for 1min between terminals and chassis without breaking insulation
Buzzer	Sound Level	
	Tone	
Bulb	Rating	12V 5W
	Base/Bulb	BA15S / G18
Luminous Intensity		3340cd or more without dome
Mass (Tolerance ±10%)		0.6kg

No.RH-100A-PDFF-EN-1_2

PATLITE Corporation

SPECIFICATIONS

Model		RH-200A
Rated Voltage		200V AC (50/60Hz)
Operating Voltage		180V to 220V AC
Current Consumption		30mA
	Buzzer	
Power Consumption		6.5W
Flashing Rate		170 Flashes Per Minute
Operating Temperature Range (Relative Humidity)		- 30°C to + 60°C (Less than 90%)
Mounting	Location	Indoor & Outdoor Use
	Direction	Indoor: Upright, Inverted & Sideways Outdoor: Upright Only
Protection Rating		IP23 (IP55 with optional rubber gasket SZ-200A)
Vibration Resistance		45.0m/s ² (33Hz, Back and Forth:2h · Right to Left:2h · Up and Down:2h)
Insulation Resistance		More than 1MΩ at 500VDC between the terminals and the chassis
Withstanding Voltage		1500VAC applied for 1min between terminals and chassis without breaking insulation
Buzzer	Sound Level	
	Tone	
Bulb	Rating	12V 5W
	Base/Bulb	BA15S / G18
Luminous Intensity		3340cd or more without dome
Mass (Tolerance ±10%)		0.6kg

No.RH-200A-PDFF-EN-1_2

PATLITE Corporation