

Base strip - DFK-PCV 6-16/ 9-GF-10,16 - 1702329

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 76 A, Rated voltage (III/2): 1000 V, Number of positions: 9, Pitch: 10.16 mm, Color: green, Contact surface: Silver, Mounting: Soldering




The figure shows a 5-pos. version of the product

Why buy this product

- ☒ Panel thickness of 1 mm to 3 mm
- ☒ Feed-through headers for use in combination with all PC 6 and PC 16 plugs
- ☒ For soldering onto the PCB
- ☒ Mounted on the housing panel by means of tool-free snap-lock mechanism or conventional screw connection



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 031158
Weight per Piece (excluding packing)	45.88 g
Custom tariff number	85366990
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length	19 mm
Pitch	10.16 mm
Dimension a	81.28 mm
Pin dimensions	1,0 x 1,2 mm
Pin spacing	10.16 mm
Hole diameter	1.7 mm

General

Range of articles	DFK-PCV 6-16/..-GF
-------------------	--------------------

Base strip - DFK-PCV 6-16/ 9-GF-10,16 - 1702329

Technical data

General

Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	1000 V
Rated voltage (III/2)	1000 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	76 A
Maximum load current	76 A
Insulating material	PA
Inflammability class according to UL 94	V0
Color	green
Number of positions	9

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27141190
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Base strip - DFK-PCV 6-16/ 9-GF-10,16 - 1702329

Approvals


Approvals

UL Recognized / SEV / cUL Recognized / CCA / EAC / IECEx CB Scheme / cULus Recognized


Ex Approvals

Approvals submitted

Approval details

UL Recognized 			
	B	C	D
Nominal current I _N	66 A	66 A	5 A
Nominal voltage U _N	300 V	300 V	600 V

SEV	
Nominal current I _N	76 A
Nominal voltage U _N	1000 V


cUL Recognized 			
	B	C	D
Nominal current I _N	66 A	66 A	5 A
Nominal voltage U _N	300 V	300 V	600 V


CCA	
Nominal current I _N	76 A
Nominal voltage U _N	1000 V

EAC

Base strip - DFK-PCV 6-16/ 9-GF-10,16 - 1702329

Approvals

IECEE CB Scheme 	
Nominal current I_N	76 A
Nominal voltage U_N	1000 V

cULus Recognized 
--

Accessories

Accessories

Coding element


Coding profile - CP-PC RD - 1701967




Coding profile, for plugging into the coding ribs of the plug at a later date, insulating material, color: Red

Drawings

Drilling diagram




Dimensioned drawing




Base strip - DFK-PCV 6-16/ 9-GF-10,16 - 1702329

Dimensioned drawing




Sheet metal cutout for snap-on.

Dimensioned drawing



Sheet metal cutout for screw connection.

Diagram



The illustration shows the derating curve for plugs DFK-PC(V) 6-16/...-G(F)(U)-(SH)-10,16 in combination with header PC 16/....-ST(F)-(SH)-10,16.