

Eaton 090798

Catalog Number: 090798

Eaton xEnergy Safety Ci LV systems LV switchgear. Flange, knockout, 6x M20, 4x M25, 4x M25/16, HxWxD=116x250x23mm

General specifications



Product Name	Catalog Number
Eaton xEnergy Safety Ci flange plate	090798
EAN	Product Length/Depth
4015080907985	115 mm
Product Height	Product Width
23 mm	205 mm
Product Weight	Compliances
0.184 kg	RoHS conform

Product specifications

Used with

250 mm (enclosure dimensions)
xEnergy Safety Ci
Basic enclosure
Accessory for basic enclosures

Special features

Sponge-rubber, captive
gasket
Quick mounting using
wedge-lock fasteners
(included as standard)

Type

Accessory for basic
enclosures
Basic enclosure
xEnergy Safety Ci

Features

Pre-stamping

Accessory/spare part type

Flanges

Unit type

Modular system

Number of connector holes

0

Suitable for nominal thread (PG) - max

25

Suitable for nominal thread (PG) - min

16

Cable entry type

4 x M25/16
4 x M25
6 x M20

Degree of protection

Other

Surface protection

Untreated

Shape

Resources

Brochures

[eaton-xenergy-safety-ci-subway-line-success-story-en-us.pdf](#)
[eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf](#)

Catalogs

[eaton-xenergy-ci-safety-catalog-ca015006en-en-us.pdf](#)

Drawings

[eaton-enclosures-flanges-xeffect-ci-enclosure-dimensions-002.eps](#)

Installation instructions

[IL0566](#)

mCAD model

[fl3_2.dwg](#)

[fl3_2.stp](#)

System overview

[eaton-insulated-boards-flanges-xenergy-safety-ci-flange-plate-explosion-drawing-006.eps](#)

Straight

Material

Plastic

Model

Cable screw gland

Thread type

Metric

Thickness

4 mm

Suitable for cable diameter - max

0 mm

Suitable for cable diameter - min

0 mm



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia