
Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



AP8958

Overview

Presentation

APC Switched Rack Power Distribution Units (PDUs) enable advanced, usercustomizable power control and active monitoring. Remote outlet level controls allow
power on/off functionality for power recycling to remotely reboot equipment and
restrict unauthorized use of individual outlets. Power sequencing delays allow users
to define the order in which to power up or down attached equipment. Avoid circuit
overload during power recovery and extend uptime of critical equipment by
prioritizing the load shedding. Current metering provides real-time remote monitoring
of connected loads. Switched Rack PDUs include real power monitoring, a
temperature/humidity sensor port, locking IEC receptacles, and low profile circuit
breakers. User-defined alarms warn of potential circuit overloads before critical IT
failures occur. Users can access, configure, and control Switched Rack PDUs
through secure Web, SNMP, or Telnet Interfaces and is complimented by APC
Centralized Management platforms using InfraStruxure Central, Capacity Manager
and Change Manager.

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Provided Equipment	Installation guide Rack Mounting brackets Serial configuration cable Safety guide

Complementary

Input Voltage	200 V	
	208 V	
	230 V	
Height	38.90 in (98.8 cm)	
Width	2.20 in (5.6 cm)	
Output Voltage	100 V	
	200 V	
	208 V	
	230 V	
Depth	1.81 in (4.6 cm)	
Net Weight	7.12 lb(US) (3.23 kg)	
Mounting Location	Side	
Mounting preference	No preference	
Input Plug Type	IEC 60320 C20	
Mounting Mode	Rack-mounted	
Rack units	0U	

Life Is On APC

Mounting position	Vertical
Line Rated Current	16 A
Permissible voltage	100240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz
Outlet type and quantity	7 IEC 60320 C13 1 IEC 60320 C19

Environment

Product Certifications	cUL Listed PSE UL Listed VCCI Class A VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003
Ambient air temperature for operation	23140 °F (-560 °C)
Relative Humidity	595 %
Operating altitude	010000 ft
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)
Storage Relative Humidity	595 %
Storage altitude	050000 ft (0.000000000015240.0000000000 m)

Ordering and shipping details

GTIN	731304277101
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	44.29 in (112.5 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	4.49 in (11.4 cm)
Package 1 Weight	10.49 lb(US) (4.76 kg)

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1302
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACh Regulation	REACh Declaration
Halogen content performance	Product contains halogen above thresholds
᠃ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Product data sheet

AP8958

Image of product / Alternate images

Alternative

