



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Shield & Strain Relief**

Cable Exit Angle: **180°**

Primary Product Material: **Carbon Steel**

Number of Positions: **16, 20, 34**

Operating Temperature (Max): **150 °C [302 °F]**

Features

Product Type Features

Connector Cover Type	Shield & Strain Relief
----------------------	------------------------

Configuration Features

Number of Positions	16, 20, 34
---------------------	------------

Body Features

Cable Exit Angle	180°
Primary Product Material	Carbon Steel

Mechanical Attachment

Thread Size	4-40
-------------	------

Dimensions

Product Width	21.03 mm[.828 in]
Product Length	62.31 mm[2.453 in]
Compatible Cable Diameter Range	12.7 mm[.5 in]
Product Height	50.8 mm[1.999 in]

Usage Conditions

--	--



Operating Temperature (Max)	150 °C[302 °F]
-----------------------------	----------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(5)



Connector Contacts(51)



Connector Hardware(46)



Power Contacts(51)



Rectangular Connector Housings(77)



Rectangular Power Connectors(82)



Standard Rectangular Connectors(81)

Customers Also Bought



TE Part #6-1415001-1
PT570L24



TE Part #4-1415033-1
PT78740

Documents

Product Drawings

34 POS. SHIELD ASSY.

English

CAD Files

Customer View Model

ENG_CVM_201571-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_201571-2_E.3d_stp.zip

English

Customer View Model

ENG_CVM_201571-2_E.2d_dxf.zip

English

3D PDF

English

Customer View Model



[ENG_CVM_CVM_201571-2_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_201571-2_J.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_201571-2_J.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[AMP Shield & Cable Clamp Assemblies \(Long Sides\) for Series "M" Connec](#)

English

Agency Approvals

[Agency Approval Document](#)

English