

137 MSP

Machine workbench clamp

| | |
|-----------------------|-------------|
| Code | ETIM |
| 6408080 | EC003935 |
| EAN | UNSPSC |
| 4010886640807 | 27-11-21-04 |
| Country of origin | eCl@ss |
| Austria | 21-04-90-90 |
| Customs tariff number | |
| 82032000 | |



Article description

- For fast, secure clamping of a variety of workpieces
- Suitable for sliding blocks with M8, M10, M12 thread
- GEDORE special vanadium steel, nickel-plated
- Release lever blue dip-insulated
- Tenon block not included

Article information

| | | | |
|--------------------------|----------------|-----------------------|---------------------------------|
| Contents [Qty of pieces] | 1 | Total length [inch] | 11 |
| Net weight [kg] | 0,79 kg | appropriate for | T-nuts with M8, M10, M12 thread |
| Total length [mm] | 280 mm | Clamping width [mm] | 100 mm |
| Material | Vanadium steel | Clamping width [inch] | 4 |