



### Datasheet

# IEC Glassfibre Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug

Types K, J or N, 2 or 5 metres long with 're-wireable' miniature flat pin plug





Type 'J'



Type 'N'

Туре 'К'

- Thermocouple types K, J & N
- Fast response, welded exposed junction
- Various lengths of glassfibre insulated flat pair cable
- Good temperature resistance (not suitable in fluids)
- 1/0.3mm conductors
- 'Re-Wireable' miniature flat pin plug
- Temperature range –60°C to +350°C (short periods up to 400°C)
- Tolerance to IEC 584 Class 2
- Colour code to IEC 584-3
- Ideal for test & development applications

Т/С Туре	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire	Allied code	RS order code
'К' 'К' 'К' 'К'	1/0.3mm 1/0.3mm 1/0.3mm 1/0.3mm	1 metres 2 metres 5 metres 10 metres	Mini plug Mini plug Mini plug Mini plug	Green Green Green Green	White White White White	70643603 70654799 70913017	872-2616 363-0294 804-7874 872-2610
ጎ, ጎ, ጎ,	1/0.3mm 1/0.3mm 1/0.3mm 1/0.3mm	1 metres 2 metres 5 metres 10 metres	Mini plug Mini plug Mini plug Mini plug	Black Black Black Black	White White White White	70643602	872-2629 363-0288 872-2622 872-2626
'N'	1/0.3mm	2 metres	Mini plug	Pink	White	70643604	363-0301

# Making your own Thermocouples?

## L60 Thermocouple & Fine Wire Welder



The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding

It is primarily designed for use by sensor manufacturers to produce commercial grade thermocouple junctions; it is ideal for producing large numbers of exposed junction thermocouples for test and development laboratories. The L60 Thermocouple Welder is ideally suited to transducer and RTD extension lead attachment

Use of the Thermocouple Welder does not require special skills and most operatives will be capable of producing quality work with little practice. The instrument is supplied with a full range of user accessories including a footswitch

Suitable for use with wires of up to 1.1mm diameter an argon gas shield facility is included but a satisfactory thermocouple junction is produced without the need for argon. The output energy of the L60 Thermocouple Welder can be varied up to 60 Joules

- Simple to use Thermocouple Welder
- Designed for the production of commercial grade thermocouple junctions (See below for range of thermocouple cables)
- Also suitable for other fine wire work
- Front panel or footswitch operation
- Argon gas shield facility

#### Supplied complete with the following accessories:

- Wire Holding Pliers & Lead
- Safety Glasses
- Magnifying Eyeglass
- Carbon Electrodes
- Spare 2A Fuse
- Argon Hose
- Mains Lead
- Footswitch for greater ease of use

#### **ORDERING INFORMATION**

#### MODEL

FINE WIRE WELDER Spare Carbon Electrodes (x5) for 1.1mm 250V Fine Wire Welder RS129/0816

	States and the states of the	Contraction of the	
a second			and a second
Company			The second second

Carbon Electrode

 Allied Code
 RS ORDER NUMBER

 70825788
 363-0351

 70656473
 814-0184

#### **SPECIFICATIONS**

#### General

Energy Output 0-60 Joules Welding Capacity Wires up to 1.1mm diameter Duty Cycle Minimum 5-10 welds/min

#### MECHANICAL

Physical Dimensions 220mm Wide x 120mm High x 250mm Depth Weight 4kg

#### ELECTRICAL

Power Supply 110-120 Vac or 220-250 Vac, 50-60Hz Power Consumption Max 170VA dropping to 20VA during charging

#### MAINTENANCE

Apart from keeping the electrode in good order, no other maintenance is required


(Front View)



(Rear View)



#### **Thermocouple Welder Controls**



А	Arc	Argon gas and weld current controlled by the "Weld" switch. LED indication
В	Purge	Allows the gas line and electrode shield to be purged of air prior to a new welding period
С	Weld Switch	Initiates a welding operation (in "arc" mode also opens the Argon valve)
D	Argon LED	Indicates when the Argon control valve is open and gas is flowing
E	Wait LED	Glows when weld charge is building
F	Ready LED	"Ready to Weld" indication
G	Power	Rotary control of the capacitor charge voltage
Н	Level Selector	Selects the total capacitance available giving the following
		values with LED indication
		"LO" = 0 to 6 Joules

"LO" = 0 to 6 Joules "MED" = 0 to 28 Joules "HI" = 0 to 64 Joules

I	Electrode Holde	r Holds the replaceable carbon electrode which is accessible by removing the outer Argon Shield
1	Ded Cecket	Output cocket for using the pliers supplied

J Red Socket Output socket for using the pliers supplied

#### K Black Socket Output socket, this provides an additional earth

# IEC PTFE Insulated Twin Twisted Pair Thermocouple Cable

Available in Thermocouple Types K, J T & N



Type 'K'

- PTFE twin twisted pair for extending or making simple thermocouples
- Single pair of PTFE insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Suitable for steam & pressure applications, autoclaves, sterilizers etc.
- 25 & 50 metre reel lengths
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to IEC-584-3

Т/С Туре	Conductors	Cores	Reel Length	Allied code	RS order code
1 1	1/0.2mm 1/0.2mm	+Black/-White +Black/-White	25 metres 50 metres	70657194 70657195	827-5980 827-5984
Ј К К Т Т	1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm	+Black/-White +Black/-White +Green/-White +Green/-White +Brown/-White +Brown/-White	25 metres 50 metres 25 metres 50 metres 25 metres 50 metres	70657198 70657199 70657200 70657205 70657208 70657206	827-5993 827-5996 827-6000 827-6019 827-6028 827-6022
K K	1/0.508mm 1/0.508mm 1/0.508mm 1/0.508mm	+Black/-White +Black/-White +Green/-White +Green/-White	25 metres 50 metres 25 metres 50 metres	70657197 70657201 70657203 70657204	827-5990 827-6003 827-6012 827-6016
J K T N	7/0.2mm 7/0.2mm 7/0.2mm 7/0.2mm	+Black/-White +Green/-White +Brown/-White +Pink/-White	25 metres 25 metres 25 metres 25 metres	70657202 70657207 70657209 70657210	827-6006 827-6025 827-6031 827-6034

# IEC PVC Insulated Flat Pair Thermocouple Extension & Compensating Cable

PVC Insulated Flat Pair (to IEC-584)



- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types for K, J, T & N

RS129/0816

- Compensating types VX (KCB) & U (RCA) for types K & R/S Thermocouples respectively
- Stranded conductors available, either 7/0.2mm or 13/0.2mm
- Available in 10, 25, 100 & 200 metre lengths
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to IEC-584-3

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exten	ision:					
КΧ	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
КΧ	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
КΧ	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
КΧ	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
КΧ	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657079	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70641737	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
ТΧ	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
ТΧ	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
ТΧ	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
ТΧ	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
ТΧ	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Compensating:						
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	70657082	827-5609
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	70641629	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	70657080	827-5603
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	70641630	219-4573
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	70657083	827-5612
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647
RS129/0816						

## **IEC PTFE Single Shot Thermocouple Cable**

Type K, 10 metre reel




- Thermocouple type K
- 10 metre spool length
- 7/0.2mm diameter conductor
- Operating range: -75°C to +250°C
- Teflon insulated single shot construction
- Resistant to chemicals, oils and fliuds
- Suitable for aerospace applications and is widly used in autoclaves
- Colour coded to IEC-584-3

Туре	Outer	Length	Allied code	RS Code
К	Green/White	10 metres	70657216	827-6053

## ANSI PFA Insulated Twin Twisted Pair Thermocouple Cable

Available in Thermocouple Types K & T (ANSI MC96.1)




- PFA Teflon<sup>®</sup> twin twisted pair for extending or making simple thermocouples
- Single pair of PFA insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam etc.
- Thermocouple types K & T with 1/0.2mm OR 1/0.3 conductors. 7/0.2mm option available for type K
- 25, 50 & 100 metre reel lengths
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to ANSI MC96.1

RS129/0816

<b>T/C Type</b>	<b>Conductors</b>	Cores	<b>Reel Length</b>	Allied code	RS order code
KX	1/0.2mm	+Yellow/-Red	25 metres	70656106	814-0030
KX	1/0.2mm	+Yellow/-Red	50 metres	70656111	814-0049
KX	1/0.2mm	+Yellow/-Red	100 metres	70656109	814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
ТХ	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
ТХ	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
ТХ	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109

## **ANSI PVC Thermocouple Extension & Compensating Cable**

PVC Insulated Flat Pair (ANSI MC96.1)



- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types for K, J, & T
- Compensating types VX (KCB) for types K Thermocouples
- Stranded conductors available, 7/0.2mm
- Available in 25, 100 & 200 metre lengths
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to ANSI MC96.1

Т/С Туре	Conductors	Cores	Jacket	Reel Length	Allied code	RS order code
Extension:						
KX	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656102	814-0018
KX	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656105	814-0027
КХ	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656103	814-0020
XL	7/0.2mm	+ White/-Red	Black	25 m	70656096	813-9995
XL	7/0.2mm	+ White/-Red	Black	100 m	70656098	814-0005
JX	7/0.2mm	+ White/-Red	Black	200 m	70656099	814-0008
ТХ	7/0.2mm	+Blue/-Red	Blue	25 m	70656119	814-0074
ТХ	7/0.2mm	+Blue/-Red	Blue	100 m	70656122	814-0083
ТХ	7/0.2mm	+Blue/-Red	Blue	200 m	70656123	814-0086
Compensating	g:					
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656127	814-0103
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656130	814-0112
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656131	814-0115